


NON-INSULATED FLAG TERMINALS

Specifications

- **Terminal Material:** Brass
- **Plating:** Electro Tin Plated



Ordering Information:


Wire Range AWG / mm ²	NTE Part Number	Dimensions inch(mm)			
		NEMA Tab	B	L	E
22 – 18 AWG 0.5 – 1.5mm ²	76-FT22	.032 x .250 (0.8 x 6.4)	.260 (6.6)	.551 (14.0)	.283 (7.2)
16 – 14 AWG 1.5–2.5mm ²	76-FT16	.032 x .250 (0.8 x 6.4)	.260 (6.6)	.551 (14.0)	.283 (7.2)
12 – 10 AWG 4–6mm ²	76-FT12	.032 x .250 (0.8 x 6.4)	.260 (6.6)	.583 (14.8)	.354 (9.0)

NYLON INSULATED FLAG TERMINALS



Specifications

- **Maximum Electrical Rating:** 300 Volts
- **Maximum Temperature:** +105°C
- **Terminal Material:** Brass
- **Plating:** Electro Tin Plated
- **Insulation Material:** Easy Entry Nylon



Ordering Information:

Wire Range AWG / mm ²	NTE Part Number	Dimensions inch(mm)						
		NEMA Tab	B	L	F	E	D	d1
22 – 18 AWG 0.5 – 1.5mm ²	76-NIFT22	.032 x .250 (0.8 x 6.4)	.260 (6.6)	.634 (16.1)	.311 (7.9)	.591 (15.0)	.177 (4.5)	.067 (1.7)
16 – 14 AWG 1.5–2.5mm ²	76-NIF16	.032 x .250 (0.8 x 6.4)	.260 (6.6)	.634 (16.1)	.311 (7.9)	.591 (15.0)	.177 (4.5)	.091 (2.3)