




TECHNICAL SPECIFICATIONS		
A	3.94"	100.00mm
B	7.50"	190.50mm
C	7.88"	200.00mm
D	3.94"	100.00mm
E	2.95"	75.00mm
F	7.88"	200.00mm
G	0.77"	19.56mm
H	9.13"	231.78mm
I	10.81"	274.64mm
J	4.00"	101.60mm
K	10.25"	260.35mm
L	5.00"	127.00mm
M	8.25"	209.55mm



- Fast install fixed wall mount.
- Slide together mounting plates for quick install/removal
 - Very low profile: .75" (19mm) from wall
 - "Hot Swap" capable
 - Includes security hardware
 - Includes complete mounting hardware kit
 - VESA compliant: 75 to 200x200
 - 175 lb. (79.4 kg) max weight capacity
 - Available in Platinum