

COIL:

RESISTANCE 330 Ω ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 13.0 VDC
 MUST RELEASE 2.0 VDC MIN.


ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES:


OPERATE 13 MS MAX.
RELEASE 5 MS MAX.
CONTACT BOUNCE 5 MS MAX (NC)
2 MS MAX (NO)

CUSTOMER DATA SHEET



CONTACT RATING: 10A 30 VDC RES.
10A 115 VAC 400 HZ., 6A 30 VDC
INDUCTIVE 100,000 OPERATIONS

DR. R. B. 7-10-91 OK. 7/10/91 *[Signature]*



CUST. HI-G
 CUST. NO. 2T-1D-126

TYPE "07" RELAY

B07B932BZ1-8011