




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF L-COM, INC.. ANY REPRODUCTION IN PART OR WHOLE
WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	RELEASED FOR PRODUCTION	12/14/01	MCCORMICK
B	ECN 3128: UPDATE DWG FORMAT	12/20/05	D.GRIFFIN
C	ECN 3776: UPDATED DIMENSIONS, NEW FORMAT	12/30/08	D.FRISIELLO



"F" JACK



UHF JACK

NOTES:

MATERIALS:

SHELL: BRASS
CONTACTS: BRASS
INSULATOR: DELRIN
CENTER PIN: BRASS

FINISH:

SHELL: NICKEL PLATE
CONTACT: GOLD PLATE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = .3 .XX = .15 PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY MCCORMICK	12/05/01		
	CHECKED BY D.PARHAM	12/05/01	CATEGORY COAXIAL	
	APPROVED BY R.CARRICK	12/05/01	PRODUCT DESCRIPTION UHF JACK TO TYPE F JACK	
COLOR VARIATIONS MAY OCCUR		SIZE A	FSCM NO. 43321	DWG. NO. BA301
REF		SCALE: NONE	CAD FILE: BA301.SLDDRW	REV. C
		SHEET 1 OF 1		