

596-00496

Article Number: 596-00496



Pre-Printed Solar Label, "WARNING - ELECTRICAL SHOCK HAZARD W/DC", 3.75" X 2.5", Vinyl, Orange/White, 50/RL



Download spec sheet

Base Data

Local Order Number 596-00496

Type WESHLBLDC

Color Orange (OG)

Features and Benefits

- Made with UV stable inks and materials for durability and weather resistance.
- The labels are supplied with aggressive adhesive to ensure long life.
- Solar Installation labels meet NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Product Description

HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the 2014 National Electrical Code (NEC 2014) and the 2012 International Fire Code (IFC 2012) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Technical Description

3.75" X2.5" Black text on an Orange/White background that reads as: "WARNING - ELECTRICAL SHOCK HAZARD. DO NOT TOUCH TERMINALS. TERMINALS ON BOTH LINE AND LOAD SIDE MAY BE ENERGIZED IN THE OPEN POSITION. DC VOLTAGE IS ALWAYS PRESENT WHEN SOLAR MODULES ARE EXPOSED TO SUNLIGHT" - 50 per roll

Local Order Number 2 Spanish Version: 596-00802

Short Description

Pre-Printed Solar Label, "WARNING - ELECTRICAL SHOCK HAZARD W/DC", 3.75" X2.5", Vinyl, Orange/White, 50/RL

Product Dimensions

Length L (Imperial) 3.75 "

Length L (Metric) 95.25 mm

Width W (Imperial) 3.75 "

Width W (Metric) 95.25 mm

Height H (Imperial) 2.5 "

Height H (Metric) 63.5 mm

Logistics and Packaging

Quantity Per roll

Package Quantity 50

Package Quantity (Metric) 50

Labels per Column 1

Labels per Row 1

Material and Specifications

|                                       |                                                                 |
|---------------------------------------|-----------------------------------------------------------------|
| <b>Material</b>                       | Type 443/552, UV Stable Flexible White Vinyl w/Acrylic Laminate |
| <b>Material Shortcut</b>              | 443/552                                                         |
| <b>Adhesive</b>                       | Acrylic                                                         |
| <b>Adhesive Shortcut</b>              | Acrylic                                                         |
| <b>Adhesive Operating Temperature</b> | -40°F to +174°F (-40°C to +79°C)                                |
| <b>Halogenfree</b>                    | Yes                                                             |
| <b>Operating Temperature</b>          | -40°F to +174°F (-40°C to +79°C)                                |
| <b>ROHS Compliant</b>                 | Yes                                                             |
| <b>Certification/Specification</b>    | UL969                                                           |
| <b>UL Recognized (US)</b>             | Yes                                                             |