



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		REVISED PER ECO-15-015252	16NOV15	BJ	FY



RECOMMENDED P.C. BOARD LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE	03MAR05	TE Connectivity	
		CHK A. SHARPE	01/22/92		
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	ASSEMBLY, PIN, RIGHT ANGLE, HDI, LEAD-FREE, 4 ROW, WITHOUT GUIDES, 3.05[.120] SOLDER POSTS
		0 PLC ± -		PRODUCT SPEC	
		1 PLC ± -		APPLICATION SPEC	
		2 PLC ± -		SIZE	A1
		3 PLC ± 0.13 [.005]		CAGE CODE	00779
		4 PLC ± -		DRAWING NO	5533286
		ANGLES ± -		RESTRICTED TO	
MATERIAL		FINISH		WEIGHT	
				SCALE	4:1
		CUSTOMER DRAWING		SHEET	1 OF 2
				REV	A

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

1

HOUSING MATERIAL: THERMOPLASTIC.

2

CONTACT MATERIAL: COPPER ALLOY.

3

FINISH:
MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108–9063; BASED ON TELCORDIA DR–1217–CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
TIN PLATED SOLDER TAILS.

4

RIGHT ANGLE PIN RECOMMENDED P.C. BOARD HOLE SIZES ARE 0.94–1.09 [.037–.043]; RECOMMENDED PAD DIA IS 1.52 [.060].

5

MOUNTING EARS AND HARDWARE PURCHASED SEPARATELY, KIT PART NUMBER 533050–1.

6

HOUSINGS WITH CENTER MOUNTING ARE RECOMMENDED FOR ASSEMBLIES WITH 75 CONTACTS PER ROW OR MORE.

7

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

6

7

OBSOLETE

187.96 [7.400]	74	191.77 [7.550]	201.93 [7.950]	209.55 [8.250]	300	—1=5533286–2—
149.86 [5.900]	59	153.67 [6.050]	163.83 [6.450]	171.45 [6.750]	240	5533286–9
111.76 [4.400]	44	115.57 [4.550]	125.73 [4.950]	133.35 [5.250]	180	5533286–6
99.06 [3.900]	39	102.87 [4.050]	113.03 [4.450]	120.65 [4.750]	160	5533286–5
78.74 [3.100]	31	82.55 [3.250]	92.71 [3.650]	100.33 [3.950]	128	5533286–3
73.66 [2.900]	29	77.47 [3.050]	87.63 [3.450]	95.25 [3.750]	120	5533286–2
60.96 [2.400]	24	64.77 [2.550]	74.93 [2.950]	82.55 [3.250]	100	5533286–1
E	D	C	B	A	POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
J. POLIGNONE
CHK
A. SHARPE
APVD
A. SHARPE

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± 0.13 [.005]
4 PLC ± –
ANGLES ± ± –

1

2

3

DWN
J. POLIGNONE
CHK
A. SHARPE
APVD
A. SHARPE

03MAR05
03MAR05
03MAR05

NAME
ASSEMBLY, PIN, RIGHT ANGLE, HDI, LEAD–FREE,
4 ROW, WITHOUT GUIDES,
3.05[.120] SOLDER POSTS

SIZE
A1

CAGE CODE
00779

DRAWING NO
5533286

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
A

4805 (1/15)