





FRONT VIEW

1,310
[33.27]

655
[16.64]

695
[17.65]

880
[22.35]


2,240
[56.9]

2,055
[52.2]

$\varnothing .092 \pm .002$
[2.34 ± 0.0]

$\varnothing .004$ [4 PLC]

OF -B-



THIS DRAWING IS CONTROLLED THROUGHOUT THE PROJECT BY THE DESIGNATION DATE OF REVISIONS AND THE DATE OF THIS DRAWING. SHOULD BE CONTACTED FOR THE LATEST VERSION.						DWN BY B. MCMASTER	11JULY05	tyco <i>Electronics</i>		AMP Incorporated Harrisburg, PA 17105-3608	
						CHE BY S. SHUEY	11JULY05				
DIMENSIONS: INCHES [mm]						TOLERANCES, UNLESS OTHERWISE SPECIFIED:	APO BY S. SHUEY	11JULY05	NAME GUIDE ASSEMBLY, DIE-CAST, LONG COVER, MEDIA CONVERTER MODULE, CHAMP BLINDMATE		
						Ø P L/C ± Ø P L/C ± Ø P L/C ± Ø0.050 (.13) Ø P L/C ± ANGLES ±	PRODUCT SPEC APPLICATION SPEC	SIZE CASE CODE DRAWING NO		RESTRICTED TO	
MATERIAL						FINISH	WEIGHT -	A 00779 C = 5390317			
							CUSTOMER DRAWING		SCALE 2:1	SHEET 1 OF 1	REV A