

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301070030](#)
Status: **Active**
Overview: [Stringlights](#)
Description: Super-Safeway Assembled Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead with Guard 3.04m (10.0'), Overall Length 30.48m (100.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130107](#)
NEMA Configuration NEMA 5-15
NEMA Rating Rain Tight
Outlet None
Overview [Stringlights](#)
Product Name Super-Safeway
Type String Lights
UPC 78678879626

Physical

Cord Length - Primary 3.04m (10.0')
Cord Length - Secondary N/A
Depth 46.48mm (1.830")
Duty Industrial
Guard Included Yes
Guard Type Steel
Height 101.60mm (4.000")
Length 30.48m (100.0')
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Stringer
Packaging Type Carton
Socket Construction Assembled

Electrical

Bulb Type Incandescent
Cord Type - Primary 12/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 200W
Lumens 2000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 310123



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130107](#) Series