


PART NUMBER

10118241-001RLF







PART NO. DESCRIPTION:

10118241-00XXLF


RoHS COMPATIBLE
 PACKING TYPE
 R:TAPE & REEL
 CONTACT AREA PLATING
 1:Au 15u"

NOTES:

1. MATERIAL:
 HOUSING: LCP+30%GF ,UL94 V-0,BLACK
 TERMINAL: COPPER ALLOY.
 SHELL: STAINLESS STEEL
2. FINISH:
 CONTACT AREA: GOLD PLATED
 CONTACT SOLDER AREA: GOLD FLASH PLATED
 SHELL: TIN PLATED
 UNDER NICKEL PLATED OVER ALL.
3. PRODUCT SPECIFICATION: GS-12-0983.
4. PACKAGING SPECIFICATION: GS-14-2164.
5. THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
6. THE CONNECTOR CAN WITHSTAND EXPOSURE TO 260 DEGREE C PEAK TEMPERATURE FOR 10 SECONDS IN IR REFLOW OVEN.



RECOMMENDED PCB LAYOUT (.XX±0.05)
 CONNECTOR SIDE (TOP VIEW)



mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family HDMI		
ltr	ecn no	dr	date	tolerances unless otherwise specified			title		
A		LS	09/13/11	angles	.X±0.25	MM	HDMI TYPE D RECEPTACLE		
B	ELX-N-16493	Henry	06/24/14	lineal	.XX±0.20				
				X°±1°	.XXX±0.10	scale	dwg no		
				dr	LEIF SHEN	09/13/11	sheet 1 of 1		
				enrg	LEIF SHEN	09/13/11	10118241		
				chr	GARY HSIEH	09/13/11	type		
				appd	GARY HSIEH	09/13/11			
sheet	revision	B					CUSTOMER Drawing		
index	sheet	1							