




Features

- Surface Mount 4 mm Square / Multiturn Cermet / Industrial / Sealed
- Halogen free** with date code 114
- Sealed to withstand board wash processing
- Pick and place centering design, with flush adjustment

- 4 mm design meets EIA/EIAJ/IPC/VECI SMD standard trimmer footprint
- RoHS compliant* - see [processing information](#) on RoHS compliant surface mount trimmers
- For trimmer applications/processing guidelines, [click here](#)

3214 - 5-Turn Trimpot® Trimming Potentiometer

Electrical Characteristics

Standard Resistance Range	 10 ohms to 2 megohms
	(see standard resistance table)
Resistance Tolerance	 ±10 % std.
Absolute Minimum Resistance	 1 % or 2.0 ohms (whichever is greater)
Contact Resistance Variation	 3 % or 3 ohms max.
Resolution	 Essentially Infinite
Insulation Resistance	 500 vdc.
	100 megohms min.
Dielectric Strength	
Sea Level	 600 vac (1 minute)
Adjustment Angle	 5 turns nom.

Environmental Characteristics

Power Rating (300 volts max.)	
85 °C	 0.25 watt
150 °C	 0 watt
Temperature Range	 -65 °C to +150 °C
Temperature Coefficient	 ±100 ppm/°C
Seal Test	 85 °C Fluorinert†/60 seconds
Humidity	 MIL-STD 202 Method 106
	TRS ±2 %; IR 10 megohms
Vibration	 20 G TRS±1 %; VRS ±1 %
Shock	 100 G TRS ±1 %; VRS±1 %
Load Life	
.....@ 85 °C rated power 1,000 hours	
TRS	3 ohms or 3 % (whichever is greater)
Rotational Cycling	 200 cycles
TRS	3 ohms or 3 % (whichever is greater)
Thermal Shock	 5 cycles
TRS	±2 %; VRS ±1 %

Physical Characteristics


Mechanical Stop	 Wiper idles
Torque	 180 g-cm max.
Weight	 Approximately 0.01 oz.
Marking	 Manufacturer's code, resistance code and date code
Solderability	 Per MIL-STD-202, Method 208
Wiper	 50 % (Actual TR) ±10 %
Flammability	 UL94V0
Pushover Strength	
J, G	 4.4 lbs.
W, X	 1 lb.
Adjustment Tool	 H-91

How To Order


Model	3214 J - 1 - 502 E
Style	
Standard or Modified	
Product Indicator	
-1 = IR Reflow (standard)	
†-2 = Wave Solderable	
-FW5 = .070" ± .010" Shaft Extension	
Resistance Code	
Embossed Tape Designator	
E = Style J, G: 500 pcs./7" reel (standard)	
Style W: 250 pcs./7" reel (standard)	
Style X: 200 pcs./7" reel (standard)	
G = Style J, G: 1500 pcs./13" reel (standard)	
Style W: 1000 pcs./13" reel (standard)	
Style X: 850 pcs./13" reel (standard)	
G = Style J, G: 1500 pcs./13" reel (FW5)	
Style W, X: 600 pcs./13" reel (FW5)	
Consult factory for other available options.	
†-2 has a treated stainless steel shaft	

Product Dimensions


3214J Side Adjust




3214W Top Adjust



3214G Side Adjust



3214X Top Adjust



*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

**Bourns follows the prevailing definition of "halogen free" in the industry.

Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

†"Fluorinert" is a registered trademark of 3M Co. Specifications are subject to change without notice.



The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

3214 - 5-Turn Trimpot® Trimming Potentiometer

BOURNS®


Packaging Specifications

J & G Styles




* Embossed Tape Designator "E"
 ** Embossed Tape Designator "G"
 (See How To Order chart for further information.)


Cover tape peel strength: Meets EIA specification 481.



W Style



W & X Style Reel




* Embossed Tape Designator "E"
 ** Embossed Tape Designator "G"
 (See How To Order chart for further information.)

Cover tape peel strength: Meets EIA specification 481.

DIMENSIONS: $\frac{\text{MM}}{(\text{INCHES})}$
 TOLERANCES: $\pm \frac{0.25}{(.010)}$ EXCEPT WHERE NOTED

X Style



Standard Resistance Table

Resistance (Ohms)	Resistance Code
10	100
20	200
50	500
100	101
200	201
500	501
1,000	102
2,000	202
5,000	502
10,000	103
20,000	203
50,000	503
100,000	104
200,000	204
500,000	504
1,000,000	105
2,000,000	205

Popular distribution values listed in boldface.
 Special resistances available.

REV. 08/14

"Trimpot" is a registered trademark of Bourns, Inc.
 Specifications are subject to change without notice.
 The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
 Users should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[3214J-2-503E](#) [3214X-2-503E](#) [3214W-1-253E](#) [3214X-2-202E](#) [3214J-2-202E](#) [3214W-2-204E](#) [3214G-1-500E](#) [3214J-1-501E](#) [3214W-1-500E](#) [3214J-1-500E](#) [3214W-1-502G](#) [3214X-1-500E](#) [3214X-1-501E](#) [3214W-1-502E](#) [3214G-1-504E](#) [3214W-1-504G](#) [3214G-1-502E](#) [3214J-1-502E](#) [3214W-1-504E](#) [3214X-1-502E](#) [3214X-1-504E](#) [3214J-1-504E](#) [3214X-2-203E](#) [3214X-2-204E](#) [3214X-2-205E](#) [3214W-2-203E](#) [3214J-2-203E](#) [3214W-2-201E](#) [3214X-2-201E](#) [3214X-2-200E](#) [3214W-2-502E](#) [3214W-2-202E](#) [3214W-2-501E](#) [3214W-1-102G](#) [3214W-1-501G](#) [3214G-1-205E](#) [3214W-1-223E](#) [3214J-2-102E](#) [3214X-2-102E](#) [3214W-2-102E](#) [3214X-2-502E](#) [3214X-1-100E](#) [3214W-1-102E](#) [3214J-1-100E](#) [3214J-1-103G](#) [3214J-1-103E](#) [3214J-1-104E](#) [3214G-1-100E](#) [3214W-1-104G](#) [3214J-1-104G](#) [3214G-1-104E](#) [3214X-1-104E](#) [3214W-1-100E](#) [3214X-1-102E](#) [3214G-1-102E](#) [3214W-1-104E](#) [3214J-1-102E](#) [3214X-1-103E](#) [3214G-1-105E](#) [3214W-1-105E](#) [3214W-1-103E](#) [3214X-1-101E](#) [3214J-1-101E](#) [3214X-1-105E](#) [3214W-1-101G](#) [3214W-1-101E](#) [3214G-1-101E](#) [3214J-1-105E](#) [3214G-1-103E](#) [3214W-1-103G](#) [3214W-1-205E](#) [3214G-1-203E](#) [3214W-1-203E](#) [3214X-1-203E](#) [3214X-1-201E](#) [3214J-1-203E](#) [3214J-1-201E](#) [3214X-1-205E](#) [3214W-1-201E](#) [3214G-1-201E](#) [3214J-1-204E](#) [3214J-1-205E](#) [3214W-1-204E](#) [3214J-1-202E](#) [3214J-1-200E](#) [3214X-1-200E](#) [3214G-1-204E](#) [3214J-1-202G](#) [3214G-1-200E](#) [3214W-1-200E](#) [3214X-1-204E](#) [3214X-1-202E](#) [3214G-1-202E](#) [3214W-1-202E](#) [3214W-1-202G](#) [3214W-2-104E](#) [3214W-2-103E](#) [3214X-2-104E](#) [3214X-2-103E](#) [3214J-2-103E](#)