

Item # LC1K1210B7, TeSys K Non-reversing Contactor



TeSys K Non-reversing Contactor

TeSys K IEC Contactor - 12A - 24Vac Coil

SPECIFICATIONS

Type	TeSys K IEC Contactor - 12A - 24Vac Coil
Termination Method	Screw Clamp
Contact Rating	600V / 12A
Coil Voltage	24Vac 50/60 Hz
50/60 Hz Voltage Code	B7
Coil Consumption Inrush	30 VA
Coil Consumption Sealed	4.5 VA
Power Wire Size	#12 - #18 AWG
Power Terminal Torque	7 lb-in (0.8 Nm)
Control Wire Size	#12 - #18 AWG
Control Terminal Torque	7 lb-in (0.8 Nm)
Mounting Hardware	35mm DIN Rail, 4mm screw
Weight	0.40 lb (0.18 kg)
AC1 Resistive Rating	20 Amp

AC3 Single Phase 115V	0.5 HP
AC3 Single Phase 230V	1.5 HP
AC3 Three Phase 200V	3 HP
AC3 Three Phase 230V	3 HP
AC3 Three Phase 460V	7.5 HP
AC3 Three Phase 575V	10 HP
Control Contact Rating (0NC/1NO)	A600
Control Contact Rating (1NC/0NO)	N/A
UL File/CCN	E164353 / NKCR
CSA File	LR43364 3211 03
Meets Standard	IEC 60647-1-1
CE	Yes
RoHS	Yes