



SCHEMATIC

### MATERIALS:

Connector: 2 ea. SMA Receptacle. Body: Tarnish Resistant Plating, Center Contact: Gold Plated Beryllium Copper  
Solder Turret Terminal Screws: Steel  
Shielded Housing: Die cast aluminum alloy A380 or A384.  
Finish: Blue paint per Federal Standard 595 #25109 over Phosphoric Etch  
Cover: .040 Thick aluminum alloy #1100-H14  
Finish: Clear Anodized  
Screws: Steel 4 ea. #2-32 x 1/4" Pan Head, self-tapping

### RATINGS:

Operating Voltage: Inner conductor/Shield: 335 VRMS Max.  
Operating Temperature: -55°C to +150°C  
Nominal Impedance: 50 Ohms

### ORDERING INFORMATION: Model 2399

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

2399