

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

E

D


C

B



A

B-FORMAT 2002

REVISIONS



OPTIONAL INSULATING BARRIER



BOTTOM VIEW

TERMINAL OPTIONS:

- $.187''$ (4.75mm) x $.032''$ (.81mm) Solderless
- $.110''$ (2.79mm) x $.032''$ (.81mm) Solderless
- $.187''$ (4.75mm) x $.020''$ (.51mm) Solderless
- $.110''$ (2.79mm) wide with $.048''$ (1.22mm) x $.237''$ (6.02mm) Slot for Soldering

DIMENSIONS IN INCHES (MILLIMETERS)
DO NOT SCALE DRAWING


Dwg. No.

GRS-4011B-XXXX

MOUNTING PANEL THICKNESS

Standard—.050" (1.27mm) to .150" (3.81mm).
Optional Mounting Claws for Custom Panel thickness are available.

**PANEL PIERCING
POLARIZED**



TAB AND POLARIZATION OPTIONS

CW INDUSTRIES
Southampton, Pa. 18966

TOLERANCES UNLESS OTHERWISE SPECIFIED
2 Place Decimal $\pm .010$ METRIC
3 Place Decimal $\pm .005$ 1 Place Dec. $\pm .25$ mm
Angles $\pm 1^\circ$ 2 Place Dec. $\pm .13$ mm

Made for: CW IND.
Drawn by: DGW 10-28-2010
Checked by:
Approval:

Title: **ROCKER
SWITCH
ASSEMBLY
S.P./S.T. MOM.**

Division: **SWITCH**
Dwg. No. **GRS-4011B-XXXX**