

LAMP DATA

653690 = 388

T-1½ Sub-Miniature								
Volts	Amps	Lumens	MSCP	Life (hours)	Filament shape	T-1½ 6mm Bi-Pin	T-1½ 6mm Midget Flange SX6s	T-1½ 6mm Midget Groove S5.7s
1.35	0.06	0.1	0.01	500	C-2R		331	
2.7	0.06	0.5	0.04	6,000	C-2R		338	
5	0.06	0.6	0.05	25,000	C-2R	3149	3150	
5	0.06	0.6	0.05	25,000	C-2R		3150-203*	
5	0.115	1.9	0.15	40,000	C-2R	7362	7335	
6	0.10	2.5	0.20	5,000	C-2R		723	
6	0.20	7.5	0.60	1,000	C-2R	7328	328	
6.3	0.20	5.0	0.40	20,000	C-2V	7381	381	379
6.3	0.20	6.9	0.55	3,000	C-2R	7349	349	
10	0.04	1.0	0.08	5,000	C-2F	7367	367	
12	0.04	1.5	0.12	10,000	C-2F	7371	394	7354
12	0.09	4.0	0.32	20,000	C-2V		740	
12	0.10	5.0	0.40	5,000	C-2V		725	
14	0.037	1.6	0.13	5,000	C-2F		733	
14	0.08	3.8	0.30	15,000	C-2F	7382	382	386
14	0.08	6.3	0.50	1,500	C-2F	7330	330	336
18	0.04	1.9	0.15	10,000	C-2F	7370	370	
24	0.05	4.2	0.33	5,000	C-2F			783
24	0.08	6.5	0.52	5,000	C-2F		789	
28	0.024	1.7	0.14	4,000	C-2F		1116	784
28	0.04	2.5	0.20	20,000	C-2F	7374	385	7355
28	0.04	3.8	0.30	10,000	C-2F	7387	387	* 388 *
28	0.04	3.8	0.30	10,000	C-2F		387-203*	
28	0.04	4.3	0.34	4,000	C-2F	7327	327	334
28	0.04	4.5	0.36	4,000	C-2F		727	
NOTES All dimensions in mm. Drawings not to scale This sheet lists a selection of available lamps See next page for additional types Please enquire for other ratings and sizes Special options: Aged and selected, Colour coated bulbs Silicone rubber filters						Pin diameter 0.5	* with internal insulating sleeve	