

► Heatsinks f.cool

► Cases f.case

▼ **Connectors f.con**

► Sockets

▼ PCB connectors

■ Male headers

■ **Female headers**

■ Direct female connectors

■ Jumpers

► IDC-connectors

► D-Sub connectors

■ Brackets for PC

► Optoelectronics

Female headers

SL 1 ... / SL 11 ...

SL 1 053 7 Z

one row, □ 0.635 mm

Data sheet

add to request



Features

Technical Drawing

Variants

Service

Accessories / related products

grid	2.54 mm
no. of contacts	7
contact material	CuSn alloy
surface of contact	tin-plated
surface contact /	Ni+≥0.2µm Au
contact sleeve	Ni+4...6µm Sn
version	standard
volume resistance	≤5 mΩ
nominal current	3 A
nominal voltage	250 V AC
test voltage	2000 V
insulating body material	PA 4.6. GF
temperature range	-40°C... +163°C (260°C/10 s)
class of flammability	UL 94 V-0
specific insulation resistance	>10.0 ⁷⁰ Ω·m
connection type	-
reflow solderable	yes