



Common mode choke

Order code	TCK-076
Inductance	Pin 1-2: 55 $\mu\text{H} \pm 35\%$ (at 100 kHz / 20 mV) Pin 3-4: 55 $\mu\text{H} \pm 35\%$ (at 100 kHz / 20 mV)
Rated current	5.7 A max.
DCR	Pin 1-2: 8.5 m Ω Pin 3-4: 8.5 m Ω
Rated voltage	500 VDC
Operating temperature	-40 to +105°C

Impedance curve



Dimensions [mm]

A	11.7 max.
B	11.7 max.
C	8.8 max.
D	2.5 min.
E	7.62 ± 0.2
F	7.62 ± 0.2
G	$\varnothing 0.6 \pm 0.1$