

TLS 2200® / TLS PC Link™ Label Index by Size




Diagram	Part Number	Pieces Per Package	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Write-On Height C Inch (mm)	Maximum Characters Per Line For Font: 2	Maximum Lines Of Text For Font: 2
1.000" Label Width (continued)									
▲	PTL-19-499	250	Nylon Cloth	White	1.000 (25.40)	1.000 (25.40)		24	10
■	PTL-19-642	250	Tedlar®	White	1.000 (25.40)	1.000 (25.40)	0.375 (9.53)	24	3
■	PTL-103-427	250	Vinyl	White	1.000 (25.40)	1.250 (31.75)	0.500 (12.70)	24	5
▲	PTL-31-498	250	Vinyl Cloth	White	1.000 (25.40)	1.500 (38.10)		24	16
■	PTL-31-427**	250	Self-laminating Vinyl	Translucent	1.000 (25.40)	1.500 (38.10)	0.500 (12.70)	24	5
■	BPTL-31-427	2500	Self-laminating Vinyl	Translucent	1.000 (25.40)	1.500 (38.10)	0.500 (12.70)	24	5
▲	PTL-31-498	250	Vinyl Cloth	White	1.000 (25.40)	1.500 (38.10)		24	16
▲	PTL-31-499	250	Nylon Cloth	White	1.000 (25.40)	1.500 (38.10)		24	16
■	PTL-31-642	250	Tedlar	White	1.000 (25.40)	1.500 (38.10)	0.500 (12.70)	24	5
■	PTL-21-427**	100	Self-laminating Vinyl	Translucent	1.000 (25.40)	2.500 (63.50)	0.750 (19.05)	24	8
▲	PTL-21-498	100	Vinyl Cloth	White	1.000 (25.40)	2.500 (63.50)		24	23
■	BPTL-21-427	1000	Self-laminating Vinyl	Translucent	1.000 (25.40)	2.500 (63.50)	0.750 (19.05)	24	8
▲	PTL-21-498	100	Vinyl Cloth	White	1.000 (25.40)	2.500 (63.50)		24	23
▲	PTL-21-499	100	Nylon Cloth	White	1.000 (25.40)	2.500 (63.50)		24	23
■	PTL-21-642	100	Tedlar	White	1.000 (25.40)	2.500 (63.50)	0.750 (19.05)	24	8
■	PTL-64-427***	100	Self-laminating Vinyl	Translucent	1.000 (25.40)	3.375 (85.73)	1.125 (28.58)	24	12
■	PTL-23-427**	100	Self-laminating Vinyl	Translucent	1.000 (25.40)	4.000 (101.60)	1.000 (25.40)	24	10
■	BPTL-23-427	1000	Self-laminating Vinyl	Translucent	1.000 (25.40)	4.000 (101.60)	1.000 (25.40)	24	10
▲	PTL-23-498	100	Vinyl Cloth	White	1.000 (25.40)	4.000 (101.60)		24	23
●	PTL-42-422	1	Polyester	White	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-430	1	Polyester	Clear	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-432	1	Polyester	Clear	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-439	1	Vinyl	White	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-439-BK	1	Vinyl	Black	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-439-BL	1	Vinyl	Blue	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-439-GN	1	Vinyl	Green	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-439-OR	1	Vinyl	Orange	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-439-RD	1	Vinyl	Red	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-439-YL	1	Vinyl	Yellow	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-483	1	Polyester	White	1.000 (25.40)	50 ft (15.24 m)		50	10
●	PTL-42-489	1	Polyester	White	1.000 (25.40)	50 ft (15.24 m)		50	10
1.100" Label Width									
■	PTL-105-427-AW		Self-laminating Vinyl	Translucent	1.100 (27.94)	0.250 (6.35)		24	3
1.130" Label Width									
▶	PTL-24-423-BK	500	Polyester	White	1.130 (28.70)	0.500 (12.70)		24	3
▶	PTL-24-428-BK	500	Metallized Polyester	Silver	1.130 (28.70)	0.500 (12.70)		24	3
▲	PTL-24-483-BK	500	Polyester	White	1.130 (28.70)	0.500 (12.70)		24	3
▲	PTL-24-486-BK	500	Polyester	Silver	1.130 (28.70)	0.500 (12.70)		24	3
1.180" Label Width									
❖	PTLFP-01-8425	250	Polypropylene	White	1.180 (30.00)	0.788 (20.00)		26	3
✱	PTLFT-01-8425	250	Polypropylene	White	1.180 (30.00)	0.788 (20.00)		26	3
1.206" Label Width									
■	PTL-111-145-GY	100	Polyethylene	Gray	1.206 (19.25)	0.758 (30.63)		24	3

Tedlar® is a registered trademark of DuPont.

Any label two inches or larger in width is rotated on liner.

Note: Labels in chart are sorted in order by width, height, 3 digit material number (within part number), then die number (within part number).

****Also available in:** BL=blue, BR=brown, GN=green, GY=grey, OR=orange, PL=purple, RD=red, YL=yellow.

To order a color, add a dash "-" after the material number, then add the color suffix.

Standard product: Contact your Brady Identification Solutions distributor or Customer Service representative for ordering information.

***** PTL-64-247 has two write-on areas, one at each end of the label.**