




NOTE:

1. TEST:DC 300V/1s
2. INSULATION RESISTANCE:10m ohm
3. CONTACT RESISTANCE:2 ohm
4. PRODUCTS MEASURE UP TO THE ROHS
5. PVC TEGMENT

|    |                                                                                                                                              |       |
|----|----------------------------------------------------------------------------------------------------------------------------------------------|-------|
| 10 | PE BAG 6" *9" *0.04MM                                                                                                                        | 1PCS  |
| 9  | ELLIPTICAL CABLE TIE WITH CORE L=70MM                                                                                                        | 1PCS  |
| 8  | TIN WIRE LEAD--FREE Ø0.6 ROHS                                                                                                                | 0.45g |
| 7  | P1&P2 PVC , BLACK 45P                                                                                                                        | 16g   |
| 6  | CONDUCTIVE COPPER PLATINUM P1.W:25MM* L:45MM 1PCS ; P2.W:20MM* L:35MM 1PCS                                                                   | 2PCS  |
| 5  | GUIMMED PAPER P1.W:20* L:50MM; P2.W:15* L:35MM                                                                                               | 2PCS  |
| 4  | PE1&P2 TRANSPARENT PE INTERNAL MODEL MATERIALS,LOW DENSITY                                                                                   | 6g    |
| 3  | HDMI C TYPE MALE: SHORT BODY PIN G/F,IRON SHELL--PLATED NICKEL,INSULATION BLACK                                                              | 1PCS  |
| 2  | HDMI A TYPE MALE: SHORT BODY PIN G/F,IRON SHELL--PLATED NICKEL,INSULATION BLACK                                                              | 1PCS  |
| 1  | UL2027/6[30AWG(7/0.10TS)*1P+EA+AL/M]*4+30AWG(7/0.10TS)*1P+30AWG(7/0.10TS)*5C+AE8(16/6/0.12AM) OD:6.0mm PVC BLACK TEGUMENT CUT L=990±10mm(Ls) | 1PCS  |
| No | DESCRIPTION                                                                                                                                  | QTY   |

| P2<br>MC/TYPE | P1<br>HDMI A/TYPE | P2<br>HDMI C/TYPE | P1<br>HDMI A/TYPE |
|---------------|-------------------|-------------------|-------------------|
| 1             | 2 GND             | 13                | 17 RED            |
| 2             | 1 RED             | 14                | 13 GRAY           |
| 3             | 3 WHITE           | 15                | 15 YELLOW         |
| 4             | 5 GND             | 16                | 16 ORANGE         |
| 5             | 4 GREEN           | 17                | 14 PURPLE         |
| 6             | 6 WHITE           | 18                | 18 WHITE          |
| 7             | 8 GND             | 19                | 19 PINK           |
| 8             | 7 BLUE            | SHELL             | BRAID             |
| 9             | 9 WHITE           |                   | SHELL             |
| 10            | 11 GND            |                   |                   |
| 11            | 10 BROWN          |                   |                   |
| 12            | 12 WHITE          |                   |                   |

|                                            |               |                                 |       |      |         |
|--------------------------------------------|---------------|---------------------------------|-------|------|---------|
| -TOLERANCES-<br>UNLESS OTHERWISE SPECIFIED |               | CnC Tech, LLC                   |       |      |         |
| 公差參考表                                      |               | TITLE: HDMI A/M TO CM CABLE PVC |       |      |         |
| X.X ±0.38                                  | X.X° ±3.00°   | PRODUCT NO: 742-10010-00100     |       |      |         |
| X.XX ±0.25                                 | X.XX° ±2.00°  | DATE                            | SCALE | UNIT | PAGE    |
| X.XXX ±0.10                                | X.XXX° ±1.00° | 2013.08.20                      | 1:1   | mm   | Z 1 / 1 |