



## Shrink-Kon®

### PLG250-0-E

General purpose, flexible heat shrink tubing for the protection, insulation and bundling of cables.

<b>T&amp;B Catalog Number:</b>	<b>PLG250-0-E</b>
<b>EAN Number:</b>	05414363076957
<b>UPC Number:</b>	78621053227
<b>Description:</b>	PLG thin wall flexible heat shrink tubing, with expanded diameter 6.4 mm, black, shrink ratio 2:1, length 75 m

#### Technical Information

Tubing Family	PLG
Wall Thickness	thin
Shrink Ratio	2:1
Tube Characteristics	single wall
Material	PE crosslinked polyolefin
Temperature Range	-55°C to +125°C
Shrink Temperature	> +110°C
IP Rating	IP60
Flammability Rating	self-extinguishing
Colour	black
Silicone free	yes
Lead/Cadmium free	yes
Dielectric Strength	20 KV/mm
Chemical Resistance	good

#### Ordering Information

Expanded Diameter as Supplied (inch)	1/4
Expanded Diameter as Supplied (mm)	6.4
Fully Recovered Diameter (mm)	3.2
Wall Thickness before Shrinking (mm)	0.3
Wall Thickness after Shrinking (mm)	0.6
Length (m)	75
Packaging Type	reel