




PIN SUPPLIED LOOSE PRE-INSERTED INTO GROMMET



SNAP RIVET LOCATES INTO A 7 mm [.276] DIA. HOLE, IN A 2.5±0.5 mm [.098±.020] THICK PANEL.




P/N: SRRCT-1



SR-6060B PIN SUPPLIED WITH TIE, NOT INSERTED
(ALSO SEE NOTE 5.)



SNAP RIVET LOCATES INTO A 7 mm [.276] DIA. HOLE, IN A 2.5±0.5 mm [.098±.020] THICK PANEL.



P/N: SRRCT-2

NOTES:

1. MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01)
2. COLOR: BLACK.
3. MAX BUNDLE DIA.: 40 [1.58]
4. MAX. LOOP TENSILE STRENGTH: 250 NEWTONS [56 LBS].
5. RIVET PIN MATERIAL: NYLON 6 UL 94 V-2 (RMS-52).
FOR MORE DETAILS SEE DRAWING "SR" (P/N: SR-6060B).
6. ALTERNATE UNITS FOR REFERENCE ONLY.

A	RELEASED, SEE ECN #1186	SK	06/27/06
REV.	DESCRIPTION	ENGR.	DATE

TITLE: SNAP RIVET RELEASABLE CABLE TIE						DWG IN MM [IN]	
CREATED USING SOLIDWORKS	FILE #: SRRCT-X		DWN: SK	APP: SK		FINAL	
TOLERANCES UNLESS NOTED 0-10=±0.1 10.01-30=±0.3 30.01-50=±0.5 ANG.=±1°	SHEET: 1 OF 1		SHEET SIZE: B		DT: 06/27/06		CHKD: S.J.
	RE: RICHCO, INC.		RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060		PART # SEE DRAWING		PRINT TYPE CA