



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			B	REV PER ECR 10-004647	02MAR10	JR

AMP WIRE RANGE	FILE E13288	LR7189 Certified
1/0 AWG SOLID OR STRANDED	1/0 AWG STRANDED	1/0 AWG SOLID OR STRANDED

- 1 COPPER PER ASTM B-152, ANNEALED
- 2 TIN PLATE 0.00254 [.000100] MIN TIN PER ASTM B-545



100	LOOSE PIECE	55821-1
QTY	PACKAGING TYPE	PART NO.

MAX RECOMMENDED OPERATING TEMPERATURE: 170°C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 10/23/91		 Tyco Electronics Corporation Harrisburg, PA 17105-3608						
	VOLTAGE RATING: N/A	DIMENSIONS: MM [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.20[.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK BR BARE 10/24/91	NAME TERMINAL, RING TONGUE, SOLISTRAND, WIRE SIZE: 50.0mm2 [1/0 AWG] -						
		APVD JL MECKLEY 10/24/91									
CIRCULAR MIL AREA: 42.4-60.6mm² [83,700-119,500] SOLID OR STRANDED		FINISH 	PRODUCT SPEC -	SIZE A3				CAGE CODE 00779	DRAWING NO C-55821	RESTRICTED TO -	
			APPLICATION SPEC -								
			MATERIAL	WEIGHT -	CUSTOMER DRAWING				SCALE 2:1	SHEET 1 OF 1	REV B