


	10	9	8	7	6	5	4	3	2	19203
	MATERIAL NO.	ENG. NO.	STUD SIZE	"S" MAX	DESCRIPTION					
	192030388	B-S-137-10	10	.212/5.38	LOOSE					
F	192030052	B-S-137-10T	10	.212/5.38	TAPE					



- NOTE(S):
1. MATERIAL: STEEL
 2. WIRE SIZE: 16-14 AWG (1.5-2.5 MM²)
 3. FINISH: NICKEL PLATING
 4. PART IS ROHS COMPLIANT.
 5. AMBIENT OPERATING TEMPERATURE UP TO 900 °F (483 °C).

ADDED OPERATING TEMP EC NO: ETC2007-0297 DRWN:HEILE CHKD: JMACNEIL APP: JMACNEIL	2007/03/13 2007/03/13 2007/03/14	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY DMYRICK	DATE 2005/04/06	TITLE RING TONGUE TERMINAL, 16-14 AWG, KRIMPTITE, 900 DEG F (483 DEG C)		
				4 PLACES	± ---	± ---	CHECKED BY RDEROSS	DATE 2005/04/06			
				3 PLACES	± ---	± ---	APPROVED BY RDEROSS	DATE 2005/04/06	MOLEX INCORPORATED		
				2 PLACES	± ---	± ---	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-19203-017			SHEET NO. 1 OF 1
				1 PLACE	± ---	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE B THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
				ANGULAR ± ---°							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[19203-0052](#) [19203-0388](#)