

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [52045-3045](#)
Status: **Active**
Overview: FFC-FPC (Through-Hole)
Description: 1.25mm Vertical, Non-ZIF Receptacle, 30 Circuits

Documents:

3D Model	Product Specification PS-52045-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E29179
----	--------

General

Product Family	FFC/FPC Connectors
Series	52045
Overview	FFC-FPC (Through-Hole)
Product Name	N/A
UPC	800753571631

Physical

Circuits (Loaded)	30
Color - Resin	Gray
Contact Position	N/A
Entry Angle	Vertical
Mated Height	8.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	2345.600/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Retention	None
Packaging Type	Tray
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.914µm
Plating min - Termination	0.914µm
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Kinked Pin
Wire/Cable Type	FFC/FPC

Electrical

Current - Maximum per Contact	0.5A, 1A
Voltage - Maximum	200V

Material Info

Reference - Drawing Numbers

Product Specification	PS-52045-001, RPS-52045-003, RPS-52045-006
Sales Drawing	SD-52045-**45




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[52045Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com