



EIA -Based VectorPak™ Subrack Systems


Rack Accessories

Blank Front Panels - FP87-19

Blank Front Panels is supplied with slots to fit sidewall mounting flanges. Customer drills holes to match sidewalls and attaches with user supplied hardware. Panels are 1/8" thick brushed aluminum with clear chromate finish.

Side Dress Panels

Side Filler Panels are 3" wide, slotted to fit sidewall mounting flanges and drilled for screws. Customer cuts to width needed to close gap between end modules and sidewalls. To attach side panels use HA12 handles or user supplied hardware. Panels are 0.8" thick brushed aluminum with clear chromate finish.



Rack with HFP52-1 Hinged Front Panel (side)

Side Hinged Front Panels - HP52-1

Side Hinged Front Panels, for card protection and improved appearance, come in an easily assembled kit form which includes the hinged panel with latch, striker plate and 2 filler panels. Panels are 1/8" thick brushed aluminum with clear chromate finish.

Top and Bottom Card Rack Covers - CAC1, CAC2, CAC3

Two 1/16" thick aluminum covers with clear chromate finish provide dust protection for 19" wide card and module racks. Supplied with screws. Holes drilled by user per instructions provided.



Bottom Hinged Front Panels - HFP52-1

These are designed for use as a front "drop-down" panel with lanyard for holding the panel at 90°. Provides a work surface and prevents damage to equipment. Comes complete with hardware and full instructions. Panels are 1/8" thick brushed aluminum with clear chromate finish.



EIA Sub racks

Use With Rack Size				Front Panels Hinged		Cover Panels Top & Bottom		Lanyard Part No.	Blank Panel Part No.	Dimensions Front					Dim. Only G	Side Dress Panels Part No.	Handles Part No.
	Height	Width	Depth	Side Part No.	Bottom Part No.	Top Part No.	Rear Part No.			A	B	D	E	F			
3U	5.25"	19.00"	9.00"	HP52-1	HFP52-1	CAC1	CRK3	L20	FP52-19	5.25"	1.50"		2.25"		4.25"	FP52-2	HA12
3U	5.25"	19.00"	12.00"	HP52-1	HFP52-1	CAC2	CRK3	L20	FP52-19	5.25"	1.50"		2.25"		4.25"	FP52-2	HA12
3U	5.25"	19.00"	15.75"	HP52-1	HFP52-1	CAC3	CRK3	L20	FP52-19	5.25"	1.50"		2.25"		4.25"	FP52-2	HA12
4U	7.00"	19.00"	9.00"		HFP69-1	CAC1			FP69-19	7.00"	1.50"		4.00"		3.09"	FP69-2	HA13
4U	7.00"	19.00"	12.00"		HFP69-1	CAC2				7.00"	1.50"		4.00"		3.09"	FP69-2	HA13
4U	7.00"	19.00"	15.75"		HFP69-1	CAC3				7.00"	1.50"		4.00"		3.09"	FP69-2	HA13
5U	8.75"	19.00"	9.00"		HFP87-1	CAC1		L20	FP87-19	8.75"	1.50"	5.75"	2.25"	1.75"	4.25"	FP87-2	HA12
5U	8.75"	19.00"	12.00"		HFP87-1	CAC2		L20	FP87-19	8.75"	1.50"	5.75"	2.25"	1.75"	4.25"	FP87-2	HA12
5U	8.75"	19.00"	15.75"		HFP87-1	CAC3		L20	FP87-19	8.75"	1.50"	5.75"	2.25"	1.75"	4.25"	FP87-2	HA12

