


FEATURES AND PATTERN

www.dbmlighting.com

13 mm SERIES - 6° Half Angle - Part number 0-002s

Lens Reference	DBM13A-7P-GDW-2
Tested with LED	Golden Dragon warm white SM series
HAD*	6 deg
Curve Type	PEAK
Lens Material	PMMA HT
Operating temperature	-40°C+110°C




*HAD = Half Angle Divergence




OPTICAL EFFICIENCY

Half Angle Divergence:	6 deg
HAD Efficiency:	35 %
Collection Efficiency:	89 %



OUTPUT DISTRIBUTION


LED Flux: 35 Lumens at 350 mA



ILLUMINANCE

LED Flux: 35 Lumens at 350 mA

ILLUMINANCE VALUES AT VARIOUS DISTANCES			
RANGE	1.0 m	2.0 m	3.0 m
ILLUMINANCE	234 Lux	58 Lux	26 Lux
MULTIPLICATOR RATE LED+LENS / LED ONLY	20 X		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DBM Optix:](#)

[O-002s](#)