



English



[Suppliers](#)

[Investor Relations](#)

[Contact Us](#)



[Home](#) [Products](#) [Division | Brand](#) [Literature](#) [Where To Buy](#) [Careers](#) [About Us](#)

Enter keyword

Enter part number

Search

[Home](#) > [3104 06 00](#) > [3102 06 00](#) > [E0540 2-008](#) > [8A-LB8L-T-SS](#)

8A-LB8L-T-SS



DESCRIPTION	ATTRIBUTE VALUE
PRODUCT TYPE	PROCESS VALVE BALL
PRESSURE RATING	1000 PSIG (69 BAR)
CONFIGURATION	2-WAY INLINE
SIZE	1/2"
CONNECTION	DOUBLE FERRULE COMPRESSION
TEMPERATURE RATING	-65 F TO 350 F (-54 C TO 177 C)
FLOW RATE	CV = 5.1
BODY MATERIAL	STAINLESS STEEL
SEAL MATERIAL	PTFE
SEAT MATERIAL	PTFE
OPERATED	MANUAL
MOUNT	
ADDITIONAL DETAIL	
TRADE/BRAND NAME	
SYNONYM	BALL VALVE

[Where to Buy](#)

[Contact Us](#)

[View All Parts](#)

[Download 3D Model](#)

No CAD available