ART-CASE

Uniquely styled electronic enclosures

The ART-CASE plastic enclosures series sets new standards for design and function with four uniquely contoured shapes: “round”, “square”, “oval” and “edge”

- attractive eye-catching design for indoor electronics used in the living and working environments
- four designs in two standard colors
- huge range of possible combinations for mobile, desktop, wall or ceiling mounted applications
- order the basic case then select either a bottom lid or base section
- top convex (H) or flat with recessed area (F)
- lid screw fitted to the bottom
- base 30° or 55° inclined for user-friendly installation and assembly angles
- base level spacer for ceiling/wall mounting, incl. supports 2 x AA and strain relief
- Euro plug module according DIN VDE 0620 part 101
- battery compartment for 2 x AAA cells (accessory)
- protection class IP 40
- internal fastening pillars for PCBs etc.



ART-CASE

Applications and Examples

Ideal indoor electrical and electronic applications, e.g.

- Transmission and reception units in building services management systems and building installations
- Medical technology and health care
- Computer peripherals
- Security technology
- Sensors, optoelectronics

3D angle measurement of articulation systems on a gravity basis

Access management in care facilities

Multiple analytical resonance system

Radio paging mushroom-type button

RFID Reader for the CTV system

VIVOBASE HOME

View Customizing Options

What do you still need for your own very personal product? We can supply enclosures and tuning knobs with all necessary modifications for fitting your electronic components.
Customizing options for Art-Case

Machining

Lacquering

Printing

Laser marking

Decor foils

Special material

RFI/EMI shielding

Installation / Assembly of accessories

ART-CASE

Select Versions

B5010007
Bottom and top part R110 F
ABS (UL 94 HB)
off-white RAL 9002
ø4.33″x1.18″

B5010009
Bottom and top part R110F
ABS (UL 94 HB)
black RAL 9005
ø4.33″x1.18″

B5010107
Bottom and top part R110 H
ABS (UL 94 HB)
off-white RAL 9002
ø4.33″x1.50″

B5010109
Bottom and top part R110 H
ABS (UL 94 HB)
black RAL 9005
ø4.33″x1.50″

B5010207
Bottom and top part R110 F
ABS (UL 94 HB)
off-white RAL 9002
ø4.33″x1.50″

B5010209
Bottom and top part R110 F
ABS (UL 94 HB)
black RAL 9005
ø4.33″x1.50″

B5010307
Bottom and top part R110 H
ABS (UL 94 HB)
off-white RAL 9002
ø4.33″x1.61″

B5010309
Bottom and top part R110 H
ABS (UL 94 HB)
black RAL 9005
ø4.33″x1.61″

B5011027
ART-CASE R110 F
PC+ABS (UL 94 V-0)
off-white RAL 9002
ø4.33″x1.18″
IP 40

B5011029
ART-CASE R110 F
PC+ABS (UL 94 V-0)
black RAL 9005
ø4.33″x1.18″
IP 40

B5011127
ART-CASE R110 H
PC+ABS (UL 94 V-0)
off-white RAL 9002
ø4.33″x1.50″
IP 40

B5011129
ART-CASE R110 H
PC+ABS (UL 94 V-0)
black RAL 9005
ø4.33″x1.50″
IP 40

B5011227
ART-CASE R110 F
PC+ABS (UL 94 V-0)
off-white RAL 9002
ø4.33″x1.50″
IP 40

B5011229
ART-CASE R110 F
PC+ABS (UL 94 V-0)
black RAL 9005
ø4.33″x1.50″
IP 40

B5011327
ART-CASE R110 H
PC+ABS (UL 94 V-0)
off-white RAL 9002
ø4.33″x1.61″
IP 40

B5011329
ART-CASE R110 H
PC+ABS (UL 94 V-0)
black RAL 9005
ø4.33″x1.61″
IP 40

ART-CASE

B5012207
Bottom and top part S110F
ABS (UL 94 HB)
off-white RAL 9002
4.33″x4.33″x1.50″

B5012209
Bottom and top part S110F
ABS (UL 94 HB)
black RAL 9005
4.33″x4.33″x1.50″

B5013227
ART-CASE S110 F
PC+ABS (UL 94 V-0)
off-white RAL 9002
4.33″x4.33″x1.50″
IP 40

B5013229
ART-CASE S110 F
PC+ABS (UL 94 V-0)
black RAL 9005
4.33″x4.33″x1.50″
IP 40

B5015007
Bottom and top part O160 F
ABS (UL 94 HB)
off-white RAL 9002
6.30″x4.33″x1.18″

B5015009
Bottom and top part O160 F
ABS (UL 94 HB)
black RAL 9005
6.30″x4.33″x1.18″

B5015107
Bottom and top part O160 H
ABS (UL 94 HB)
off-white RAL 9002
6.30″x4.33″x1.50″

B5015109
Bottom and top part O160 H
ABS (UL 94 HB)
black RAL 9005
6.30″x4.33″x1.50″

B5015207
Bottom and top part O160 F
ABS (UL 94 HB)
off-white RAL 9002
6.30″x4.33″x1.50″

B5015209
Bottom and top part O160 F
ABS (UL 94 HB)
black RAL 9005
6.30″x4.33″x1.50″

B5015307
Bottom and top part O160 H
ABS (UL 94 HB)
off-white RAL 9002
6.30″x4.33″x1.61″

B5015309
Bottom and top part O160 H
ABS (UL 94 HB)
black RAL 9005
6.30″x4.33″x1.61″

B5017207
Bottom and top part E160 F
ABS (UL 94 HB)
off-white RAL 9002
6.30″x4.33″x1.50″

B5017209
Bottom and top part E160 F
ABS (UL 94 HB)
black RAL 9005
6.30″x4.33″x1.50″

ART-CASE

System components to complete

B5011117
Base
ABS (UL 94 HB)
off-white RAL 9002

B5011119
Base
ABS (UL 94 HB)
black RAL 9005

B5011217
Base 30°
ABS (UL 94 HB)
off-white RAL 9002

B5011219
Base 30°
ABS (UL 94 HB)
black RAL 9005

B5011317
Base 55°
ABS (UL 94 HB)
off-white RAL 9002

B5011319
Base 55°
ABS (UL 94 HB)
black RAL 9005

B5011847
Lid
ABS (UL 94 HB)
off-white RAL 9002

B5011849
Lid
ABS (UL 94 HB)
black RAL 9005

B5011857
Battery compartment lid
ABS (UL 94 HB)
off-white RAL 9002

B5011859
Battery compartment lid
ABS (UL 94 HB)
black RAL 9005

Accessory "battery"

A9166001
Set of battery clips, 2 x AAA
Steel
tin-plated

A9166002
Battery contact, 2 x AAA
Steel
tin-plated

A9166003
Battery holder, 2 x AAA
PA 6 (UL 94 HB)
black RAL 9005

A9190002
Set of battery clips,
2xN/2xAA/2xAAA
Steel
tin-plated

ART-CASE

B5111107
Battery compartment, 2 x AAA
ABS (UL 94 HB)
off-white RAL 9002

B5111109
Battery compartment, 2 x AAA
ABS (UL 94 HB)
black RAL 9005

Accessory "protection"

A9199005
Strain relief
PA 6
volcano

B5111707
Anti-rotation device
ABS (UL 94 HB)
off-white RAL 9002

Accessory "wall/holder"

B5111307
Wall mounting set
ABS (UL 94 HB)
off-white RAL 9002

B5111309
Wall mounting set
ABS (UL 94 HB)
black RAL 9005

Accessory "screws"

B5111201
Set of screws

ART-CASE

Accessory



A9207150
Anti-slide feet 0.256" x 0.079"
transparent

Subject to technical modification without notice. © by OKW Gehäusesysteme, Buchen/Germany.