


20W Inspection & Machine Light



 **sunnex**

- Versatile low voltage 20W halogen light
- Four options of input voltage: 12V, 24V, 110V or 240V (with built in transformer)
- Robust and durable, suitable for a wide range of applications
- Stay-put & vibration resistant flexible arm 700mm
- Spot lamp - 60mm base with a single jointed head
- On/off switch on base
- Easy to position and focus as required
- Magnetic base and protective head cover to **IP54** available
- Supplied complete with lamp
- Suitable for manufacturing machines, machine tools, graphic design, assembly, inspection and precision mechanical work

Colour	Black	Mounting base	60 x 60mm
Total length	Flex - 960mm / Spot - 260mm	Lamp housing	Polycarbonate
IP rating	IP20 (IP54 with cover)		

333903

	Mftrs. List No.	Order Code	Price Each
Flex Lamps			
12V	14320	357-7120	
24V	14420	357-7132	
230V to 12V	14120	357-7107	
110V to 12V	14470	357-7119	
Spot Lamps			
12V	14360	472-5207	
24V	14360/2	472-5219	
Accessories			
Protective head cover	14080	357-7272	
Magnetic base	14000	357-7223	
Desk clamp	14020	474-356	
Transformer 400V to 12V	74400	472-5116	
Transformer 230V to 12V	74220	472-5104	
12V, 20W halogen bulb	15140A	357-7326	
24V, 20W halogen bulb	15141A	357-7338	