

Sheetsteel housing **BGUK 3**



Advantages

Integrated Rail System for the installation of different product sizes

Excellent corrosion protection and high abrasion resistance through powder-coated surface RAL 5008

With cooling fins for optimal heat extraction

Faceplate without cooling fins for individual connection options

Integrated crane eyes

Optionally available in degree of protection IP 54

Approvals



Sheetsteel housing BGUK 3

Electrical data

Type

BGUK 3

Operating data

For power (single phase)	500 VA
For power (three phase)	400 VA
Max. Power loss (at 40 °C ambient temperature)	48 W
Enclosure suitable for protection index	IP 20

Order numbers

Order Number	BGUK 3
--------------	--------

Mechanical data

Type

BGUK 3

Terminal and mounting

Floor mounting	No
Wall mounting	Yes
Cable glanding type	M20
Cable glanding Ø	7 - 12 mm

Measures and weights

Weight	4.00 kg
Dimension (W x H x D)	230 x 270 x 210
Effective inside dimension (W)	210 mm
Effective inside dimension (D)	195 mm
Effective inside dimension (H)	220 mm
Fixing hole Ø	5.5 mm

Accessory

Front plate (optional)	-
------------------------	---

Subjects to change.