



PRODUCT NUMBER

74355






Copyright FCI.

spec ref		-		dr	Keen Wu	2010/11/05	projection	INCH / MM	size	A4	scale	2:1	
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Henry Guo	2014/03/24			ecn no				ELX-N-17279-1
				chr	-	-			rel level				Released
				appr	Rick Bian	2014/03/24			product family		-		
surface	linear	0.X	±.01/0.25		title			2X4 LNL SHIELDED	dwg no	74355		rev	
		0.XX	±.005/0.13										
		0.XXX	±.0020/0.05										
	angular	0°	±2°										www.fci.com
ISO1101													
ISO406													
ISO1302													


PRODUCT NUMBER


74355



dr	Keen Wu	2010/11/05	projection	INCH / MM	size	A4	scale	2:1		
eng	Henry Guo	2014/03/24			ecn no		ELX-N-17279-1			
chr	-	-			rel level		Released			
appr	Rick Bian	2014/03/24	product family		-					
	title		2X4 LNL SHIELDED HEADER ASSEMBLY		dwg no		74355		rev	
	www.fci.com		cat. no.		-		Product - Customer Drw		sheet 2 of 5	


COMPONENT SIDE




dr	Keen Wu	2010/11/05	projection 	INCH / MM 	size	A4	scale	2:1			
eng	Henry Guo	2014/03/24			ecn no	ELX-N-17279-1					
chr	-	-			rel level				Released		
appr	Rick Bian	2014/03/24	product family		-						
		title			2X4 LNL SHIELDED		dwg no		74355	rev	S
www.fci.com		cat. no.		-	Product - Customer Drw				sheet 3 of 5		




Copyright FCI.




KEY POSITION 1
SCALE 2:1



NO KEY
SCALE 2:1



KEY POSITION 2
SCALE 2:1



KEY POSITION 3

dr	Keen Wu	2010/11/05	projection	INCH / MM	size	A4	scale	2:1		
eng	Henry Guo	2014/03/24			ecn no	ELX-N-17279-1				
chr	-	-			rel level	Released				
appr	Rick Bian	2014/03/24	product family		-					
		title			2X4 LNL SHIELDED		dwg no		74355	
					HEADER ASSEMBLY				rev	
									S	
www.fci.com		cat. no.			-	Product - Customer Drw			sheet 4 of 5	

74355-XYZLF

LEAD FREE OPTION(NOTES 9 & 10)

KEY POSITION (NOTE 7)

- STD NO KEY	(NOTE 8)
1-KEY POSITION 1	(NOTE 7)
2-KEY POSITION 2	(NOTE 7)
3-KEY POSITION 3	(NOTE 7)

COLOR


01 LIGHT GRAY	OBS.
02 OFF WHITE	
03 DARK GRAY	OBS.
04 BLACK	
05 SLATE GRAY	OBS.
07 SILVER GRAY	
08 PEARL WHITE	OBS.
09 PEBBLE GRAY	

PIN LENGTH LEY (DIM L)

0	.200/5.08
1	.130/3.30

NOTES:

1. HEADER SHROUD
MAT'L: HIGH TEMPERATURE THERMOPLASTIC
UL-94V-0 RATED.
2. GROUND CONTACT
MAT'L: COPPER ALLOY
PLATING: 100-160 MICRO"/2.54-4.06 MICRON Sn.
3. SIGNAL CONTACT
MAT'L: COPPER ALLOY
PLATING: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT
ON CONTACT AREA OR TAIL, OPTIONALLY (78-295u") TIN ON TAIL.
4. HEADER SHIELD
MAT'L: COPPER ALLOY
PLATING: 100 MICRO"/2.54 MICRON BRIGHT
TIN OVER 50 MICRO"/1.27 MICRON NICKEL
5. LOCATION DIMENSION FROM EDGE OF PCB
TO BE DETERMINED BY CUSTOMER.
6. THIS ASSEMBLY IS UL RECOGNIZED PER FILE
E66906, VOL. 1, SECT 40 AND CSA
APPROVED PER MASTER FILE NO. LR 46923-162
7. MUST USE PLUG OF THE SAME KEY.
KEYED PLUGS WILL MATE WITH STANDARD HEADER.
8. OMIT 4th DIGIT FOR STD NO KEY PRODUCT
9. ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION
AND THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5MM
MINIMUM THICK CIRCUIT BOARD.
10. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
11. PRODUCT SPEC: gs-12-003
12. PART NUMBER WITH SUFFIX "A" IS CUSTOM TO INTENDED FOR FMLB
EXAMPLE: 74355-1041ALF

dr	Keen Wu	2010/11/05	projection 	INCH / MM 	size	A4	scale	2:1			
eng	Henry Guo	2014/03/24			ecn no		ELX-N-17279-1				
chr	-	-			rel level		Released				
appr	Rick Bian	2014/03/24	product family		-						
		title			2X4 LNL SHIELDED		dwg no		74355	rev	S
www.fci.com		cat. no.		-	Product - Customer Drw				sheet 5 of 5		