

PRODUCT DATA DRAWING

MATERIAL :

BODY, INSERT,
HEX NUT &
LOCK WASHER:

CONTACTS:

SHIM SPRING:

INSULATOR:

STAINLESS STEEL PER AMS-5640,
UNS S30300, TYPE 1

BERYLLIUM COPPER PER ASTM-B-196,
ALLOY C17300, COND. TD04

BERYLLIUM COPPER PER ASTM-B-194,
ALLOY C17200, COND. TD04

TEFLON PER ASTM-D-1710.

FINISH :

BODY, CONTACTS
& SHIM SPRING:

INSERT,
HEX NUT &
LOCK WASHER:

GOLD PER MIL-G-45204, TYPE I,
GRADE C, CLASS 0; OVER NICKEL
PER QQ-N-290, CLASS 2

GOLD PER MIL-G-45204, TYPE I,
GRADE C, CLASS 00: OVER NICKEL
PER QQ-N-290, CLASS 1

PERFORMANCE :

IMPEDANCE:

FREQ. RANGE:

DWV:



INSUL. RES.:

50 OHMS

DC-22.0 GHz

1000 VRMS

5000 MEGOHMS MIN.



SYM.	DESCRIPTION	DATE	APPR.	UNLESS OTHERWISE SPECIFIED: 1) ALL DIMENSIONS ARE AFTER PLATING. 2) BREAK CORNERS & EDGES .005 R. MAX. 3) CHAM. 1st & LAST THDS. 4) SURFACE ROUGHNESS 63 J MIL-STD-10. 5) DIAS. ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 6) REMOVE ALL BURRS.	DIMENSIONS ARE IN INCHES TOLERANCES: DECIMALS FRACTIONAL ANGULAR .X ±.030 .XX ±.015 ±1/64 .XXX ±.005 X° ±1°0' X°X' ±15'			SV Microwave, Inc. 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
-	REL.DCN 29224	12/02	STW		MATERIAL: SEE ABOVE		□" AREA:		
					FINISH: SEE ABOVE		N/A	TITLE: BMA BULKHEAD FEEDTHRU CABLE JACK RIGID MOUNT FOR .085 S.R. CABLE	
				DRAWN: BRT 11/27/02	SIZE	CAGE NO.	SCALE	DWG. NO.	
				CHECKED: STW 12/04/02	B	95077	4X	1733-6008	
				APPROVED: STW 12/04/02					