

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0524841510**  
**Status:** **Active**  
**Description:** 2.0 W/B CONN. IDT REC. HSG ASSY

**Documents:**

3D Model	Product Specification PS-52484-012 (PDF)
Drawing (PDF)	Product Specification PS-52484-021 (PDF)
Product Specification PS-51090-003 (PDF)	Product Specification PS-52484-022 (PDF)
Product Specification PS-52478-001 (PDF)	Product Specification PS-53358-001 (PDF)
Product Specification PS-52478-002 (PDF)	Product Specification PS-55460-001 (PDF)
Product Specification PS-52484-009 (PDF)	Application Specification AS-52484-001 (PDF)
Product Specification PS-52484-011 (PDF)	RoHS Certificate of Compliance (PDF)

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	IDT and Solder Connectors
Series	<u>52484</u>
Crimp Quality Equipment	Yes
Product Name	Mi II™
UPC	800754367936

**Physical**

Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	833.200/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.914µm
Plating min - Termination	0.914µm
Temperature Range - Operating	-40°C to +105°C
Wire Insulation Diameter	0.85-1.05mm
Wire Size AWG	26, 28


**Electrical**

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Application Specification	AS-52484-001
Crimp Specification	CS-52484



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contains SVHC(2015  
June 15): No

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

52484 Series

**Mates With**

51206 , 53313 , 55460 , 53358 , 53324 , 53325

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

IDT System Hand Tool	<u>0621009900</u>
----------------------	-------------------

Product Specification

PS-51090-003, PS-52478-001, PS-52478-002,  
PS-52484-009, PS-52484-011, PS-52484-012,  
PS-52484-021, PS-52484-022, PS-53358-001,  
PS-55460-001, RPS-51090-002, RPS-51090-005,  
RPS-51090-021, RPS-52484-002, RPS-52484-005,  
RPS-52484-015, RPS-52484-016, RPS-52484-017,  
RPS-52484-019, RPS-52484-020, RPS-52484-022,  
RPS-52484-023, RPS-52484-024, RPS-52484-025,  
RPS-52484-026, RPS-52969-004, RPS-52969-006,  
RPS-53358-001, RPS-54111-005, RPS-55460-015  
SD-52484-008

Sales Drawing

This document was generated on 09/23/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**