

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190700044

Status:

Active

Description:

InsulKrimp™ Ring Tongue Terminal for 18-22 AWG Wire


Documents:

Drawing (PDF)

Product Specification PS-19902-009 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Ring and Spade Terminals
Series	19070
Mil-Spec	N/A
Product Name	InsulKrimp™
Type	Ring
Physical	
Barrel Type	Closed
Flammability	94V-2
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	8 (M4)
Wire Insulation Diameter	3.70mm (.145") max.
Wire Size AWG	18, 20, 22
Wire Size mm²	0.35 - 0.80
Electrical	
CSA	LR18689
UL	E32244
Material Info	
Old Part Number	AA-232-08X
Reference - Drawing Numbers	
Product Specification	PS-19902-009
Sales Drawing	SD-19070-003



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19070Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050300
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640051200
Hand Crimp Tool	0640010300
Hand Crimp Tool	0640011200

This document was generated on 02/02/2010

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION