



General-Purpose Regulator Diodes

Nominal Zener Voltage	250 mW Low Level Cathode = Polarity Mark	250 mW Low Noise Cathode = Polarity Mark	250 mW Low Level Cathode = Polarity Mark	250 mW Low Noise Cathode = Polarity Mark	350 mW Cathode = Polarity Mark	400 mW Low Noise Low Leakage Cathode = Polarity Mark	500 mW Cathode = Polarity Mark	
(*Note 1)	(*Notes 2,3,14)		(*Notes 2,3,18)		(*Notes 2,6,17)		(*Notes 2,5,18) (*Notes 2,6,18)	
	 Glass Case 362-01		 Glass DO-204AH (DO-35) Case 299-02		 Case 318-02,-03 Style 8 SOT-23 (TO-236AA/AB)		 Glass DO-204AH (DO-35) Case 299-02	
1.8	MLL4678	MLL4614	1N4678	1N4614				
2.0	MLL4679	MLL4615	1N4679	1N4615				
2.2	MLL4680	MLL4616	1N4680	1N4616				
2.4	MLL4681	MLL4617	1N4681	1N4617			1N4370A	
2.5								
2.7	MLL4682	MLL4618	1N4682	1N4618			1N4371A	
2.8								
3.0	MLL4683	MLL4619	1N4683	1N4619			1N4372A	
3.3	MLL4684	MLL4620	1N4684	1N4620	MMBZ5226	1N5518B	1N746 A 1N5226 B	
3.6	MLL4685	MLL4621	1N4685	1N4621	MMBZ5227	1N5519B	1N747 A	
3.9	MLL4686	MLL4622	1N4686	1N4622	MMBZ5228	1N5520B	1N748 A	
4.3	MLL4687	MLL4623	1N4687	1N4623	MMBZ5229	1N5521 B	1N749 A	
4.7	MLL4688	MLL4624	1N4688	1N4624	MMBZ5230	1N5522B	1N750 A	
5.1	MLL4689	MLL4625	1N4689	1N4625	MMBZ5231	1N5523B	1N751 A	
5.6	MLL4690	MLL4626	1N4690	1N4626	MMBZ5232	1N5524B	1N752 A	
6.0					MMBZ5233			
6.2	MLL4691	MLL4627	1N4691	1N4627	MMBZ5234	BZX84C6V2	1N753 A	
6.8	MLL4692	MLL4099	1N4692	1N4099	MMBZ5235	BZX84C6V8	1N754 A 1N957 B	
7.5	MLL4693	MLL4100	1N4693	1N4100	MMBZ5236	BZX84C7V5	1N755 A 1N958 B	
8.2	MLL4694	MLL4101	1N4694	1N4101	MMBZ5237	BZX84C8V2	1N756 A 1N959 B	
8.7	MLL4695	MLL4102	1N4695	1N4102	MMBZ5238			
9.1	MLL4696	MLL4103	1N4696	1N4103	MMBZ5239	BZX84C9V1	1N757 A 1N960 B	
10	MLL4697	MLL4104	1N4697	1N4104	MMBZ5240	BZX84C10	1N758 A 1N961 B	
11	MLL4698	MLL4105	1N4698	1N4105	MMBZ5241	BZX84C11	1N962 B	
12	MLL4699	MLL4106	1N4699	1N4106	MMBZ5242	BZX84C12	1N759 A 1N963 B	
13	MLL4700	MLL4107	1N4700	1N4107	MMBZ5243	BZX84C13	1N964B	
14	MLL4701	MLL4108	1N4701	1N4108	MMBZ5244		1N5243 B	
15	MLL4702	MLL4109	1N4702	1N4109	MMBZ5245	BZX84C15	1N5244 B	
16	MLL4703	MLL4110	1N4703	1N4110	MMBZ5246	BZX84C16	1N965B	
17	MLL4704	MLL4111	1N4704	1N4111	MMBZ5247		1N966B	
18	MLL4705	MLL4112	1N4705	1N4112	MMBZ5248	BZX84C18	1N5246 B	
19	MLL4706	MLL4113	1N4706	1N4113	MMBZ5249		1N5247 B	
20	MLL4707	MLL4114	1N4707	1N4114	MMBZ5250	BZX84C20	1N967B	
22	MLL4708	MLL4115	1N4708	1N4115	MMBZ5251	BZX84C22	1N5249 B	
24	MLL4709	MLL4116	1N4709	1N4116	MMBZ5252	BZX84C24	1N5250 B	
25	MLL4710	MLL4117	1N4710	1N4117	MMBZ5253		1N968 B	
27	MLL4711	MLL4118	1N4711	1N4118	MMBZ5254	BZX84C27	1N969 B	
28	MLL4712	MLL4119	1N4712	1N4119	MMBZ5255		1N970 B	
30	MLL4713	MLL4120	1N4713	1N4120	MMBZ5256	BZX84C30	1N5251 B	
33	MLL4714	MLL4121	1N4714	1N4121	MMBZ5257	BZX84C33	1N5252 B	
36	MLL4715	MLL4122	1N4715	1N4122			1N971 B	
39	MLL4716	MLL4123	1N4716	1N4123			1N5253 B	
43	MLL4717	MLL4124	1N4717	1N4124			1N5254 B	
47		MLL4125		1N4125			1N972 B	
51		MLL4126		1N4126			1N973 B	
56		MLL4127		1N4127			1N974 B	
60		MLL4128		1N4128			1N975 B	
62		MLL4129		1N4129			1N976 B	
68		MLL4130		1N4130			1N977 B	
75		MLL4131		1N4131			1N978 B	
82		MLL4132		1N4132			1N979 B	
87		MLL4133		1N4133			1N980 B	
91		MLL4134		1N4134			1N981 B	
100		MLL4135		1N4135			1N982 B	
110							1N983 B	
120							1N984 B	
130							1N985 B	
140							1N986 B	
150							†1N987B	
160							†1N988B	
170							1N5273# B	
180							1N5274# B	
200							†1N989B	
							1N5275# B	
							†1N990B	
							1N5276# B	
							1N5277# B	
							1N5278# B	
							†1N991B	
							1N5279# B	
							†1N992B	
							1N5281# B	

□ JAN JANTX(V) available, ± 5% only.

† 1N987-1N992 supplied in DO-7 glass package.

See Notes on page 57