

[Company](#)[Products](#)[News](#)[Download](#)[Contact](#)Search **More categories below:**[Optical-Audible Signal Devices](#) | [Installation Model](#) | [Combinations](#) | [LED/Buzzer Combination 150](#)**Product Fastfinder:** **LED Buzzer EM Contin. tone**

Part number:	150.300.55
Interface:	plug-in connection with screwable connection max. 1.5 mm ² finely stranded
Fixing:	Installation mounting
Starting current:	max. 500 mA
Color:	yellow
Sound output:	80 dB
Life duration:	50,000 h (audible: min. 5,000 h)
Dimension in mm:	ø 49,5 x 74
Protection rating:	IP65
Voltage:	24V
Voltage type:	DC
Current consumption:	50 mA
Temperature range:	-20°C...+50°C
Ton type:	Contin. tone
Ton frequency:	ca. 2,8 kHz
Housing:	PC/ABS-Blend

Tone Types 1  [Manual](#)[« Back to overview](#)

©2009 WERMA. All rights reserved

The content (text, images, graphics, sound files, animation files, video files and their arrangement) of WERMA Web sites is subject to copyright and other intellectual property protection provisions. Some WERMA Web sites may contain also images that are subject to the copyright of their providers. The content of the Web sites may neither be copied for commercial use or distribution nor may these objects be modified or re-posted on other web sites without WERMA prior written permission.

We are grateful about suggestions, errors and comments on our website.