


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1120005028](#)
Status: **Active**
Overview: [PC Network Interface Cards](#)
Description: applicom PCIE2000ETH Card, Ethernet + PROFIBUS, 2 Channels, PCI Express 1x, OPC/DLL/DAS - SCADA/HMI



Series image - Reference only

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

General	
Product Family	Network Interface
Series	112000
Application	HMI, SCADA
Approvals	CE certified
Communication Speed	Ethernet: 10/100 Mbps, PROFIBUS 9.6 kbps to 1.5 Mbps
Mounting Style	PC Slot
Operating System	Windows7, Windows8/8.1, Windows Server 2003, Windows Server 2008, Windows Server 2012, Windows Vista
Overview	PC Network Interface Cards
Product Literature Order No	987650-5289
Product Name	applicom
Protocol	EtherNet, PROFIBUS
Protocol Detail	Ethernet, PROFIBUS
Slot	PCI Express 1x
Software Downloads	APP-EPB-PCIE
Type	Ethernet Card, PROFIBUS Card
UPC	883906487409
Woodhead	Yes
Physical	
Channels	2
Interface	DAServer, DDE Server, DLL, OPC DA
Net Weight	140.000/g
Network Connection Type	Ethernet: RJ45, PROFIBUS D-Sub Female (9 pin)
Packaging Type	Carton
Processor	AMD SC520
Temperature Range - Operating	0°C to +65°C
Electrical	
Current - Maximum Input	5.5W
EMC	EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 61000-6-2
Supply Voltage	3.3V
Material Info	
Engineering Number	APP-EPB-PCIE
Reference - Drawing Numbers	
Sales Drawing	SD-112000-5026-001

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[112000 Series](#)