

PANDUCT® Type S — Solid Wall Raceway



Type S Solid Wall Raceway


- Made of rigid PVC (See [pg. 34](#) for material specifications)
- Rated for continuous use temperatures up to 50°C (122°F)
- Available in a variety of colors as a standard part (See [page 36](#) for details)
- Provided with standard mounting holes (dimensions [page 31](#))
- Available without mounting holes (See ordering information below)
- Available with adhesive backing* (See [page 22](#) for details)



Type S— Raceway Standard Colors†:

	LG		DG		WH
Light Gray		Dark Gray		White	
	BL		IB		
Black		Intrinsic Blue			

Colors shown are approximate.



Ordering Information:

- Order number of feet required in multiples of 6 ft or Std. Carton quantities.
- To order duct with mounting holes, delete NM from Part Number.
- To order with pressure-sensitive adhesive mounting tape applied, add -A to Part Number.
- Part Number shown for Light Gray LG. To order other colors, substitute WH for White, DG for Dark Gray, BL for Black, and IB for Intrinsic Blue

†See [page 36](#) to determine which sizes are available in each color

Raceway Part Number	Raceway External Dimensions		Cover Part Number	Raceway Std. Ctn. Qty.	Cover Std. Ctn. Qty.	Std. Lgth
	WxH IN.	WxH (mm)				
S.5X.5LG6NM S.5X.62LG6NM S.5X1LG6NM S.5X1.25LG6NM S.5X1.75LG6NM S.5X2LG6NM	0.63 x 0.56 0.63 x 0.68 0.63 x 1.06 0.63 x 1.31 0.63 x 1.81 0.63 x 2.06	(16.0) x (14.2) (16.0) x (17.3) (16.0) x (26.9) (16.0) x (33.3) (16.0) x (46.0) (16.0) x (52.3)	C.5LG6	120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
S.75X.75LG6NM S.75X1LG6NM S.75X1.5LG6NM S.75X2LG6NM	0.88 x 0.81 0.88 x 1.06 0.88 x 1.56 0.88 x 2.12	(22.4) x (20.6) (22.4) x (26.9) (22.4) x (39.6) (22.4) x (53.8)	C.75LG6	120 ft. 120 ft. 120 ft. 120 ft.	120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
S1X1LG6NM S1X1.25LG6NM S1X1.5LG6NM S1X2LG6NM S1X2.5LG6NM S1X3LG6NM S1X4LG6NM	1.14 x 1.12 1.14 x 1.37 1.14 x 1.62 1.14 x 2.12 1.14 x 2.62 1.14 x 3.12 1.14 x 4.12	(29.0) x (28.4) (29.0) x (34.8) (29.0) x (41.1) (29.0) x (53.8) (29.0) x (66.5) (29.0) x (79.2) (29.0) x (104.6)	C1LG6	120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
S1.5X1.5LG6NM S1.5X1.5LG6NM S1.5X2LG6NM S1.5X3LG6NM S1.5X4LG6NM	1.64 x 1.12 1.64 x 1.62 1.64 x 2.12 1.64 x 3.12 1.64 x 4.12	(41.7) x (28.4) (41.7) x (41.1) (41.7) x (53.8) (41.7) x (79.2) (41.7) x (104.6)	C1.5LG6	120 ft. 120 ft. 120 ft. 120 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
S2X1LG6NM S2X1.5LG6NM S2X2LG6NM S2X2.5LG6NM S2X3LG6NM S2X4LG6NM S2X5LG6NM	2.14 x 1.12 2.14 x 1.62 2.14 x 2.12 2.14 x 2.62 2.14 x 3.12 2.14 x 4.12 2.14 x 5.12	(54.4) x (28.4) (54.4) x (41.1) (54.4) x (53.8) (54.4) x (66.5) (54.4) x (79.2) (54.4) x (104.6) (54.4) x (130.0)	C2LG6	120 ft. 120 ft. 120 ft. 60 ft. 60 ft. 60 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
S2.5X3LG6NM	2.64 x 3.12	(67.1) x (79.2)	C2.5LG6	60 ft.	120 ft.	6 ft.
S3X1LG6NM S3X1.25LG6NM S3X2LG6NM S3X3LG6NM S3X4LG6NM S3X5LG6NM	3.14 x 1.12 3.14 x 1.37 3.14 x 2.12 3.14 x 3.12 3.14 x 4.12 3.14 x 5.12	(79.8) x (28.4) (79.8) x (34.8) (79.8) x (53.8) (79.8) x (79.2) (79.8) x (104.6) (79.8) x (130.0)	C3LG6	120 ft. 120 ft. 60 ft. 60 ft. 60 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.
S4X1.5LG6NM S4X2LG6NM S4X3LG6NM S4X4LG6NM S4X5LG6NM	4.14 x 1.62 4.14 x 2.12 4.14 x 3.12 4.14 x 4.12 4.14 x 5.12	(105.2) x (41.1) (105.2) x (53.8) (105.2) x (79.2) (105.2) x (104.6) (105.2) x (130.0)	C4LG6	120 ft. 60 ft. 60 ft. 60 ft. 60 ft.	120 ft. 120 ft. 120 ft. 120 ft. 120 ft.	6 ft.

See [page 31](#) for complete listing of dimensions. *Adhesive tape is not CSA Certified.

Part Number Nomenclature —

S	.5	X	.5	LG	6	NM
↑	↑	↑	↑	↑	↑	↑
type/style	nominal width (in)		nominal height (in)	color	length (ft)	no mounting holes