

MOUNTED LED INDICATOR LIGHTS



Fig.1




Fig.2



Fig.3



Fig.4



Bezel Mounted LED Indicator Lights

The Bezel mounts are available in several styles for both T-1 (3mm) and T-1-3/4 (5mm) sizes. The T-1size uses a mounting hole of .24" and the T-1-3/4 uses .31" diameter hole. All devices greater than 2V have current limiting resistors mounted in the leads.

Retail Part No.	Bulk Part No.	Fig. No.	Fwd Curr (I _F) mA	Operating Voltage	Resistor Included	LED Emitting Color	Mounting Type	LED/Lamp Size
39-4612-05	39-4612-05BU	1	10	5V/6V	Yes	Red	Recess Chrome	3mm (T-1)
39-4612-12	39-4612-12BU	1	10	12V/14V	Yes	Red	Recess Chrome	3mm (T-1)
39-4614-05	39-4614-05BU	1	10	5V/6V	Yes	Yellow	Recess Chrome	3mm (T-1)
39-4614-12	39-4614-12BU	1	10	12V/14V	Yes	Yellow	Recess Chrome	3mm (T-1)
39-4615-05	39-4615-05BU	1	10	5V/6V	Yes	Green	Recess Chrome	3mm (T-1)
39-4615-12	39-4615-12BU	1	10	12V/14V	Yes	Green	Recess Chrome	3mm (T-1)
39-5612-05	39-5612-05BU	1	10	5V/6V	Yes	Red	Recess Chrome	5mm (T-1-3/4)
39-5612-12	39-5612-12BU	1	10	12V/14V	Yes	Red	Recess Chrome	5mm (T-1-3/4)
39-5614-05	39-5614-05BU	1	10	5V/6V	Yes	Yellow	Recess Chrome	5mm (T-1-3/4)
39-5614-12	39-5614-12BU	1	10	12V/14V	Yes	Yellow	Recess Chrome	5mm (T-1-3/4)
39-5615-05	39-5615-05BU	1	10	5V/6V	Yes	Green	Recess Chrome	5mm (T-1-3/4)
39-5615-12	39-5615-12BU	1	10	12V/14V	Yes	Green	Recess Chrome	5mm (T-1-3/4)
39-4622-05	39-4622-05BU	2	10	5V/6V	Yes	Red	Recess Black	3mm (T-1)
39-4622-12	39-4622-12BU	2	10	12V/14V	Yes	Red	Recess Black	3mm (T-1)
39-4624-05	39-4624-05BU	2	10	5V/6V	Yes	Yellow	Recess Black	3mm (T-1)
39-4624-12	39-4624-12BU	2	10	12V/14V	Yes	Yellow	Recess Black	3mm (T-1)
39-4625-05	39-4625-05BU	2	10	5V/6V	Yes	Green	Recess Black	3mm (T-1)
39-4625-12	39-4625-12BU	2	10	12V/14V	Yes	Green	Recess Black	3mm (T-1)
39-5622-05	39-5622-05BU	2	10	5V/6V	Yes	Red	Recess Black	5mm (T-1-3/4)
39-5622-12	39-5622-12BU	2	10	12V/14V	Yes	Red	Recess Black	5mm (T-1-3/4)
39-5624-05	39-5624-05BU	2	10	5V/6V	Yes	Yellow	Recess Black	5mm (T-1-3/4)
39-5624-12	39-5624-12BU	2	10	12V/14V	Yes	Yellow	Recess Black	5mm (T-1-3/4)
39-5625-05	39-5625-05BU	2	10	5V/6V	Yes	Green	Recess Black	5mm (T-1-3/4)
39-5625-12	39-5625-12BU	2	10	12V/14V	Yes	Green	Recess Black	5mm (T-1-3/4)
39-4632-05	39-4632-05BU	3	10	5V/6V	Yes	Red	Dome Chrome	3mm (T-1)
39-4632-12	39-4632-12BU	3	10	12V/14V	Yes	Red	Dome Chrome	3mm (T-1)
39-4634-05	39-4634-05BU	3	10	5V/6V	Yes	Yellow	Dome Chrome	3mm (T-1)
39-4634-12	39-4634-12BU	3	10	12V/14V	Yes	Yellow	Dome Chrome	3mm (T-1)
39-4635-05	39-4635-05BU	3	10	5V/6V	Yes	Green	Dome Chrome	3mm (T-1)
39-4635-12	39-4635-12BU	3	10	12V/14V	Yes	Green	Dome Chrome	3mm (T-1)
39-5632-05	39-5632-05BU	3	10	5V/6V	Yes	Red	Dome Chrome	5mm (T-1-3/4)
39-5632-12	39-5632-12BU	3	10	12V/14V	Yes	Red	Dome Chrome	5mm (T-1-3/4)
39-5634-05	39-5634-05BU	3	10	5V/6V	Yes	Yellow	Dome Chrome	5mm (T-1-3/4)
39-5634-12	39-5634-12BU	3	10	12V/14V	Yes	Yellow	Dome Chrome	5mm (T-1-3/4)
39-5635-05	39-5635-05BU	3	10	5V/6V	Yes	Green	Dome Chrome	5mm (T-1-3/4)
39-5635-12	39-5635-12BU	3	10	12V/14V	Yes	Green	Dome Chrome	5mm (T-1-3/4)
39-4642-05	39-4642-05BU	4	10	5V/6V	Yes	Red	Dome Black	3mm (T-1)
39-4642-12	39-4642-12BU	4	10	12V/14V	Yes	Red	Dome Black	3mm (T-1)
39-4644-05	39-4644-05BU	4	10	5V/6V	Yes	Yellow	Dome Black	3mm (T-1)
39-4644-12	39-4644-12BU	4	10	12V/14V	Yes	Yellow	Dome Black	3mm (T-1)
39-4645-05	39-4645-05BU	4	10	5V/6V	Yes	Green	Dome Black	3mm (T-1)
39-4645-12	39-4645-12BU	4	10	12V/14V	Yes	Green	Dome Black	3mm (T-1)
39-5642-05	39-5642-05BU	4	10	5V/6V	Yes	Red	Dome Black	5mm (T-1-3/4)
39-5642-12	39-5642-12BU	4	10	12V/14V	Yes	Red	Dome Black	5mm (T-1-3/4)
39-5644-05	39-5644-05BU	4	10	5V/6V	Yes	Yellow	Dome Black	5mm (T-1-3/4)
39-5644-12	39-5644-12BU	4	10	12V/14V	Yes	Yellow	Dome Black	5mm (T-1-3/4)
39-5645-05	39-5645-05BU	4	10	5V/6V	Yes	Green	Dome Black	5mm (T-1-3/4)
39-5645-12	39-5645-12BU	4	10	12V/14V	Yes	Green	Dome Black	5mm (T-1-3/4)