

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [94506-0100](#)
Status: **Active**
Description: Quick Disconnect, Safelock Female for (0.50-1.00mm²) 18-24 AWG Wire, Accepts 6.35 x 0.81mm Tab, Unplated

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-94506-001 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family Quick Disconnects
Series [94506](#)
Crimp Quality Equipment Yes
Insulated No
Product Name Safelock
Type Quick Disconnect
UPC 800754331357

Physical

Barrel Type Open
Gender Female
Glow-Wire Compliant No
Insulation None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Unplated
Material - Plating Termination Tin
Net Weight 0.710/g
Orientation Straight
Packaging Type Reel
Polarized to Mating Part Yes
Tab Thickness 0.81mm
Tab Width 6.35mm
Temperature Range - Operating -40°C to +80°C
Termination Interface: Style Crimp or Compression
Wire Size AWG 18, 20, 22, 24
Wire Size mm² 0.50 - 1.00


Electrical

Voltage - Maximum 250V

Material Info

Reference - Drawing Numbers

Product Specification PS-94506-001
Sales Drawing SD-94506-0XXX



Series

image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[94506Series](#)

Use With
[94506 Quick Disconnect Housing](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Mini-Mac™	0638060800
Applicator Rear Feed	