





AMP WIRE RANGE	Listed
8 AWG SOLID OR STRANDED	8 AWG STRANDED

LR7189 Certified	MILITARY P/N AND CLASS
8 AWG SOLID OR STRANDED	NOT APPLICABLE

1 STAMP AMP 8* APPROX AS SHOWN.



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C [338° F] MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 6.64-10.5MM ² [13,100-20,800] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	

100	LOOSE PIECE, BOX	8-32996-1
1500	ON TAPE, REEL	32996-1
100	LOOSE PIECE	32996
QUANTITY	PACKAGE TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-24-93	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 3-24-93				
		APVD DE MILLER 3-24-93	NAME			
		PRODUCT SPEC	TERMINAL, RING TONGUE, SOLISTRAND™			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		-	A2		00779	C=32996
MATERIAL COPPER PER ASTM B-152 ANNEALED		WEIGHT -	CUSTOMER DRAWING		SCALE 8:1	SHEET 1 OF 1
FINISH TIN PLATE .00254[0.000100] MIN THICK PER ASTM B545					REV D2	