







- △ HOUSINGS; POLYESTER, UL 94V-0 RATED, NATURAL
SIGNAL AND SIGNAL GROUND CONTACTS: COPPER ALLOY
UTILITY CONTACTS: PHOSPHOR BRONZE
- △ UTILITY CONTACTS: 0.76µm MIN GOLD IN CONTACT AREA,
2.54µm MIN TIN-LEAD ON PCB TAILS, OVER 1.27µm MIN NICKEL OVER ALL.
SIGNAL AND SIGNAL GROUND CONTACTS: 0.76µm MIN GOLD IN CONTACT AREA,
2.54µm MIN TIN-LEAD ON PCB TAILS, OVER 1.27µm MIN NICKEL OVER ALL.
3. ROWS A, C, D, AND F ARE SIGNAL CONTACTS. ROWS B AND E ARE SIGNAL GROUND CONTACTS.
- △ CONNECTOR SIZE CAN ACCOMMODATE INDICATED QUANTITY OF DIFFERENTIAL PAIRS.
- △ DIMENSIONS PER CUSTOMER BOARD LAYOUT.



232	113.44	106.74	88.90	88.39	72	1367680-9
208	103.28	96.58	78.74	78.23	64	1367680-8
184	93.12	86.42	68.58	68.07	56	1367680-7
160	82.96	76.26	58.42	57.91	48	1367680-6
136	72.80	66.10	48.26	47.75	40	1367680-5
112	62.64	55.94	38.10	37.59	32	1367680-4
88	52.48	45.78	27.94	27.43	24	1367680-3
64	42.32	35.62	17.78	17.27	16	1367680-2
40	32.16	25.46	7.62	7.11	8	1367680-1
N	H DIM	D DIM	B DIM	A OR C DIM	DIFF PAIRS △	PART NUMBER

TYPICAL DIMENSIONS FOR THIS CONNECTOR ASSEMBLY ARE GIVEN IN THE FOLLOWING TABLE. DIMENSIONS IN PARENTHESES ARE FOR THE LARGEST SIZE AVAILABLE.				DWN N. REESER 26MAT04		tyco Electronics Tyco Electronics Harrisburg, PA 17103-3608
DIMENSIONS:				CHK N. REESER 26MAT04		
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD N. REESER 26MAT04		
mm				PRODUCT SPEC		
				108-1985		NAME 2-DOCK HOST BRD CONNECTOR ASSEMBLY 8-72 SIGNAL DIFF. PAIR, 2 UTILITY CONTACTS PER SIDE, 3.83mm TAIL
				APPLICATION SPEC		
				114-13068		
				WEIGHT		
MATERIAL				CUSTOMER DRAWING		SIZE A 00779
						©=1367680
						SCALE 4:1
						SHEET 1 OF 1
						REV A