



621

Dual Input Differential Manometer

Features

Dual input with +/-120" H2O range.
0.001" H2O maximum resolution.
Seven units of measure (mbar, kPa, PSI, mmHg, inHg, mmH2O, inH2O).
Display - 5 digit with backlight.
Smooth - Stabilizes display when measuring fluctuating pressures.
Auto Off - Conserve battery power.

Specifications

Measurement Range: ± 120 " H2O

Display: 5 Digit LCD with backlight

Input Type: Dual Differential (1/4" Barbed)

Resolution (max): 0.001" H2O

Accuracy: +/-0.2% of full scale

Functions: One Touch Zero, Back-light, Unit Selection, Smoothing, Auto power Off

Units of Measure: 7 Units (mbar, kPa, PSI, mmHg, inHg, mmH2O, inH2O)

Battery Type: 9V alkaline

Battery Life: 80hours (Typical)

Auto Power Off: 40 minutes

Standard Accessories (Included): 9V alkaline battery (A009A), two pieces
30" silicone tube (A613), two 1/8" NPT to 1/8" barbed fittings (A603)

