









- NOTES:
1. MATERIAL:
 - 1-1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL 94V-0, BLACK
 - 1-2 SIGNAL TERMINAL AND DETECT TERMINAL: PHOSPHOR BRONZE
 - 1-3 METAL SHELL: STAINLESS STEEL
 2. FINISH:
 - 2-1 SIGNAL TERMINAL: 1.25 MICRON NICKEL MIN UNDER-PLATED, CONTACT AREA SEE TABLE, GOLD FLASH ON SOLDER AREA.
 - 2-2 METAL SHELL: GOLD FLASH PLATED AT SOLDER AREA.
 - 2-3 DETECT PIN: 1.25 MICRON NICKEL MIN UNDER-PLATED, GOLD PLATING ON CONTACT AREA, GOLD FLASH ON SOLDER AREA.
 3. PRODUCT SPECIFICATION: PS-105027-001.
 4. PACKAGE SPECIFICATION: PK-105027-001.
 5. PRODUCT COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV 2000/53/EC.

105027-0101	0.38 MICRON MIN. GOLD PLATING
105027-0001	0.76 MICRON MIN. GOLD PLATING
105027-2001	0.1 MICRON MIN. GOLD PLATING
P/N	CONTACT AREA PLATING

ADD NEW PART EC NO: SH2012-0261 DRW:GLL1 CHKD: APPR:AYIN	2012/02/10 2012/02/23	DESCRIPTION REV	QUALITY SYMBOLS <
--	--------------------------	--------------------	---



G1	SWITCH
P8	DAT1
P7	DAT0
P6	VSS
P5	CLK
P4	VDD
P3	CMD
P2	CD/DAT3
P1	DAT2
NAME	TYPE
PIN ASSIGNMENT	

SEE SHEET 1 EC NO: SH2012-0261 DRAWN: GLLI CHKD: APPR: AYIN REV	DESCRIPTION 2012/02/10 2012/02/23	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION				
			4 PLACES	± ---	± ---	DRAWN BY GLLI	DATE 2011/12/15	TITLE 1.70H TFR HEADER WITH DETECT PIN						
			3 PLACES	± ---	± ---	CHECKED BY					DATE			
			2 PLACES	± 0.15	± ---	APPROVED BY					DATE			
			1 PLACE	± 0.20	± ---	 MOLEX INCORPORATED								
			ANGULAR ± 3 °									MATERIAL NO.		DOCUMENT NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE SHEET 1			SD-105027-001					
						SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					