





1. MATERIAL:
BODY - COPPER
  DENOTES BODY IS TIN PLATED COPPER
SCREW - STEEL, ZINC PLATED
2. UL LISTED & CSA CERTIFIED FOR USE UP TO 600V & TEMPERATURE RATED 90°C
3. RATED FOR USE WITH COPPER STRANDED CODE CONDUCTOR ONLY
4. THESE PARTS ARE RoHS COMPLIANT
5. SEE PACKAGING LABEL FOR TIGHTENING TORQUE INFORMATION
6. PROFILE OF COLLAR MAY VARY BETWEEN CURVED AND FLAT.
7. PKG QTY:
C = 100
D = 250
Q = 25



														
	PANDUIT PART NUMBER	WIRE RANGE COPPER	CURRENT RATING (AMPS)	STUD SIZE IN	DIMENSIONS - IN [mm] +/- .02 [.5]									HEX SIZE*
					G	W	K	A	M	T	H	L	C (MAX)	
	CX35-36-CY	#14 AWG - #6 AWG	35	3/16"	0.23 [5.8]	0.38 [9.7]	0.19 [4.8]	1.04 [26.4]	0.38 [9.7]	0.07 [1.8]	0.49 [12.4]	0.38 [9.7]	0.22 [5.6]	SLOTTED
	CX35-36-DY	#14 AWG - #6 AWG	35	3/16"	0.23 [5.8]	0.38 [9.7]	0.19 [4.8]	1.04 [26.4]	0.38 [9.7]	0.07 [1.8]	0.49 [12.4]	0.38 [9.7]	0.22 [5.6]	SLOTTED
	CX35-36T-CY	#14 AWG - #6 AWG	35	3/16"	0.23 [5.8]	0.38 [9.7]	0.19 [4.8]	1.04 [26.4]	0.38 [9.7]	0.07 [1.8]	0.49 [12.4]	0.38 [9.7]	0.22 [5.6]	SLOTTED
	CX35-36T-DY	#14 AWG - #6 AWG	35	3/16"	0.23 [5.8]	0.38 [9.7]	0.19 [4.8]	1.04 [26.4]	0.38 [9.7]	0.07 [1.8]	0.49 [12.4]	0.38 [9.7]	0.22 [5.6]	SLOTTED
	CX70-14-CY	#14 AWG - #4 AWG (2) #14 AWG (2) #12 AWG	70	1/4"	0.31 [7.9]	0.50 [12.7]	0.25 [6.4]	1.27 [32.3]	0.50 [12.7]	0.08 [2.03]	0.57 [14.5]	0.46 [11.7]	0.28 [7.1]	SLOTTED
	CX70-14T-CY	#14 AWG - #4 AWG (2) #14 AWG (2) #12 AWG	70	1/4"	0.31 [7.9]	0.50 [12.7]	0.25 [6.4]	1.27 [32.3]	0.50 [12.7]	0.08 [2.03]	0.57 [14.5]	0.46 [11.7]	0.28 [7.1]	SLOTTED
	CX125-14SL-QY	#4 AWG - #1/0 AWG	125	1/4"	0.43 [10.9]	0.62 [15.7]	0.31 [7.9]	1.53 [38.9]	0.62 [15.7]	0.11 [2.7]	0.77 [19.6]	0.57 [14.5]	0.41 [10.4]	SLOTTED
	CX125-56SLT-QY	#4 AWG - #1/0 AWG	125	5/16"	0.43 [10.9]	0.62 [15.7]	0.31 [7.9]	1.53 [38.9]	0.62 [15.7]	0.11 [2.7]	0.77 [19.6]	0.57 [14.5]	0.41 [10.4]	SLOTTED
	CX225-56HK-QY	#2 AWG - #4/0 AWG	225	5/16"	0.56 [14.2]	.99 [25.2]	0.50 [12.7]	2.19 [55.6]	1.00 [25.4]	0.11 [2.7]	1.13 [28.7]	0.85 [21.6]	0.50 [12.7]	3/16
	CX225-56HKT-QY	#2 AWG - #4/0 AWG	225	5/16"	0.56 [14.2]	.99 [25.2]	0.50 [12.7]	2.19 [55.6]	1.00 [25.4]	0.11 [2.7]	1.13 [28.7]	0.85 [21.6]	0.50 [12.7]	3/16
	CX225-38HKT-QY	#2 AWG - #4/0 AWG	225	3/8"	0.56 [14.2]	.99 [25.2]	0.50 [12.7]	2.19 [55.6]	1.00 [25.4]	0.11 [2.7]	1.13 [28.7]	0.85 [21.6]	0.50 [12.7]	3/16

							TITLE CX SERIES COPPER MECHANICAL CONNECTORS CUSTOMER DRAWING			
							ITEM REVISION NAME N41664BA-C41664/12			
							DATASET FILE NAME C41664/12.SLDDRW			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± .XXX ± .XX ± ANGLES ±  THIRD ANGLE PROJECTION			
12	4/13	JHNU	JHNU	RGB	REPLACED MISSING "A" DIMENSION REVISED HEX SIZE FOR CX225: 3/16 WAS 9/16	N41664BA-C41664	MATERIAL SEE NOTES			
11	2/13	JHNU	JHNU	RGB	REVISED TITLE BLOCK	N41664BA-C41664	DRAWING NUMBER C41664_12			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JHNU DATE 3/06 CHK JHNU SCALE NONE			
							SHEET 1 OF 1 SIZE B			