

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [98268-0326](#)  
**Status:** **Active**  
**Overview:** [Premo-Flex™ FFC and Etched Polyimide Jumpers](#)  
**Description:** 1.25mm Pitch Premo-Flex™ FFC Jumper, Opposite Side Contacts (Type D), 26 Circuits, 0.076m Cable Length, 0.22mm Cable Thickness, Tin(Sn) Plating

**Documents:**

|                                                          |                                                            |
|----------------------------------------------------------|------------------------------------------------------------|
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Packaging Specification PK-98268-001 (PDF)</a> |
| <a href="#">Product Specification PS-98268-001 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>       |

**General**

|                         |                                                              |
|-------------------------|--------------------------------------------------------------|
| Product Family          | Cable                                                        |
| Series                  | <a href="#">98268</a>                                        |
| Comments                | Contacts on opposite sides, Type D                           |
| Crimp Quality Equipment | Yes                                                          |
| Overview                | <a href="#">Premo-Flex™ FFC and Etched Polyimide Jumpers</a> |
| Product Name            | Premo-Flex™ FFC Jumper                                       |
| UPC                     | 756054778340                                                 |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Length                  | 0.076m          |
| Circuits (Loaded)             | 26              |
| Net Weight                    | 1.774/g         |
| Packaging Type                | Bag             |
| Pitch - Termination Interface | 1.25mm          |
| Temperature Range - Operating | -40°C to +105°C |
| Wire Size AWG                 | N/A             |
| Wire/Cable Type               | Flat Flex Cable |

**Electrical**

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.4A   |
| Voltage - Maximum             | 60V AC |

**Material Info**

**Reference - Drawing Numbers**

|                         |              |
|-------------------------|--------------|
| Packaging Specification | PK-98268-001 |
| Product Specification   | PS-98268-001 |
| Sales Drawing           | SD-98268-001 |



Series

image - Reference only

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Reviewed**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[98268Series](#)

**Use With**

<a href="http://www.molex.com/link/ffc-fpc.html">Molex FFC – FPC connector</a>.  
Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION