


General ordering data

Order No.	1565270000
Part designation	KLIPPON K41
Version	Housings, 81 mm, 120 mm, 122 mm, Aluminium alloy (AlSi12)
EAN	4008190184636
Qty.	1 pc(s).

Dimensions

Fixing dimension, width	106 mm
Height	81 mm
Length	120 mm
Width	122 mm

General details

Cover fixing	4 stainless steel M6 screws
Enclosure fixing	Holes 6 mm
Integral fixing	threaded holes M6
Resistance to shocks	10 J
Sealing material	Neoprene
Version cover	closed
Surface finish	untreated
Class of protection to EN 60529	IP 66 and IP 67
Weight	840 g
Ambient temperature, min.	-30 °C
Ambient temperature, max.	80 °C

Screwed cable glands top/bottom

M 12	6
M 16	6
M 20	3
M 25	2
M 32	1
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	4
M16	4
M20	2
M25	1
M32	1
On housing side	left / right

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000058
ETIM 3.0	EC000058
eClass 4.1	27-14-12-06
eClass 5.0	27-14-91-07
eClass 5.1	27-14-91-07

Similar products

Order No.	Part designation	Version
9529200000	KLIPPON K41 RAL7001	Housings, 81 mm, 120 mm, 122 mm, Aluminium alloy (AlSi12)