


Visit AVX's Website at www.avxcorp.com

Radial/SkyCaps

Dimensions: Millimeters (Inches)



SR21

10

AVX Style	Width (W)	Height (H)	Thickness (T)	Lead Spacing (LS)	Lead Diameter (LD)
SR15	3.810 (0.150)	3.81 (0.150)	2.540 (0.100)	2.54 (0.100)	0.508 (0.020)
SR20	5.080 (0.200)	5.08 (0.200)	3.175 (0.125)	2.54 (0.100)	0.508 (0.020)
SR21	5.080 (0.200)	5.08 (0.200)	3.175 (0.125)	5.08 (0.200)	0.508 (0.020)
SR27	6.604 (0.260)	6.35 (0.250)	4.060 (0.160)	7.62 (0.300)	0.508 (0.020)
SR30	7.620 (0.300)	7.62 (0.300)	3.810 (0.150)	5.08 (0.200)	0.508 (0.020)
SR40	10.160 (0.400)	10.16 (0.400)	3.810 (0.150)	5.08 (0.200)	0.508 (0.020)

Stock No.	Mfr.'s Type	Cap. pF	Voltage	Tol.	Temp. Coefficient	EACH			
						1-24	25-99	100-499	500-Up
881-5100	SR305A103JAA	10000	50	5	NPO	1.63	1.11	.91	.75
881-3400	SR151A100JAA	10	100	5	NPO	.51	.28	.21	.16
881-5105	SR211A100JAA	10	100	5	NPO	.58	.33	.25	.18
881-5110	SR151A150JAA	15	100	5	NPO	.46	.26	.20	.13
881-5112	SR151A150JAA	15	100	5	NPO	.58	.33	.25	.18
881-5114	SR151A180JAA	18	100	5	NPO	.51	.28	.21	.16
881-5118	SR151A220JAA	22	100	5	NPO	.33	.18	.13	.10
881-5122	SR151A270JAA	27	100	5	NPO	.51	.28	.21	.16
881-3402	SR151A300JAA	33	100	5	NPO	.51	.28	.21	.16
881-5126	SR151A390JAA	39	100	5	NPO	.51	.28	.21	.16
881-3403	SR151A470JAA	47	100	5	NPO	.51	.28	.21	.16

Stock No.	Mfr.'s Type	Cap. pF	Voltage	Tol.	Temp. Coefficient	EACH			
						1-24	25-99	100-499	500-Up
881-5128	SR211A470JAA	47	100	5	NPO	.74	.42	.32	.24
881-5130	SR211A560JAA	56	100	5	NPO	.49	.29	.21	.16
881-5132	SR151A680JAA	68	100	5	NPO	.51	.28	.21	.16
881-5136	SR151A820JAA	82	100	5	NPO	.51	.28	.21	.16
881-5138	SR151A101JAA	100	100	5	NPO	.51	.28	.21	.16
881-5164	SR211A101JAA	100	100	5	NPO	.74	.42	.32	.24
881-5168	SR151A151JAA	150	100	5	NPO	.49	.28	.22	.17
881-5172	SR151A181JAA	180	100	5	NPO	.58	.33	.25	.18
881-5176	SR211A221JAA	220	100	5	NPO	.86	.48	.36	.28
881-5178	SR151A271JAA	270	100	5	NPO	.59	.33	.25	.18
881-5182	SR151A31JAA	330	100	5	NPO	.59	.33	.25	.18
881-5184	SR151A391JAA	390	100	5	NPO	.59	.33	.25	.18
881-3408	SR151A471JAA	470	100	5	NPO	.64	.37	.28	.21
881-5190	SR211A561JAA	560	100	5	NPO	.74	.42	.32	.24
881-3409	SR151A681JAA	680	100	5	NPO	.55	.33	.23	.19
881-5194	SR201A821JAA	820	100	5	NPO	.52	.35	.29	.24
881-3410	SR201A102JAA	1000	100	5	NPO	.54	.37	.31	.24
881-3411	SR211A102JAA	1000	100	5	NPO	.54	.37	.31	.24
881-5200	SR211A152JAA	1500	100	5	NPO	.81	.55	.45	.36
881-5204	SR211A222JAA	2200	100	5	NPO	.99	.67	.54	.44
881-5206	SR211A332JAA	3300	100	5	NPO	1.09	.74	.60	.49
881-5208	SR211A472JAA	4700	100	5	NPO	1.14	.77	.64	.52
881-5210	SR301A103JAA	10000	100	5	NPO	1.63	1.11	.91	.75
881-3506	SR151A303KAA	33	100	10	NPO	.40	.21	.16	.12
881-3406	SR151A221JAA	220	100	10	NPO	.43	.25	.19	.15
881-5212	SR151C103JAA	10000	60	5	XTR	.74	.42	.32	.24
881-5222	SR215C103JAA	10000	50	5	XTR	.53	.36	.29	.24
881-3486	SR205C104JAA	100000	50	5	XTR	1.02	.70	.57	.47
881-3322	SR155C103KAA	10000	50	10	XTR	.26	.18	.16	.12
881-5224	SR155C223KAA	22000	50	10	XTR	.41	.22	.18	.13
881-5226	SR155C473KAA	47000	50	10	XTR	.58	.33	.25	.18
881-3340	SR205C104KAA	100000	50	10	XTR	.40	.26	.21	.15
881-3365	SR151C104KAA	100000	50	10	XTR	.43	.26	.21	.16
881-5228	SR215C104KAA	100000	50	10	XTR	.51	.34	.28	.23
881-5230	SR215C224KAA	220000	50	10	XTR	.92	.64	.52	.42
881-3322	SR305C334KAA	330000	50	10	XTR	1.58	1.08	.87	.73
881-5234	SR305C474KAA	470000	50	10	XTR	1.89	1.30	1.04	.85
881-3386	SR305C105KAA	1000000	50	10	XTR	1.79	1.04	.77	.62
881-5238	SR305C225KAA	2200000	50	10	XTR	9.90	6.89	5.50	4.50
881-3246	SR401C105KAA	10000000	50	20	XTR	2.72	1.86	1.52	1.24
881-3310	SR151C102KAA	10000	100	10	XTR	.41	.22	.18	.13
881-3341	SR201C102KAA	10000	100	10	XTR	.49	.26	.20	.16
881-3314	SR151C222KAA	2200	100	10	XTR	.41	.22	.18	.13
881-3316	SR211C322KAA	3300	100	10	XTR	.41	.22	.18	.13
881-3318	SR151C472KAA	4700	100	10	XTR	.46	.25	.19	.15
881-3319	SR211C472KAA	4700	100	10	XTR	.49	.26	.20	.16
881-3420	SR151C103KAA	10000	100	10	XTR	.49	.29	.20	.16
881-3353	SR201C103KAA	10000	100	10	XTR	.49	.26	.20	.16