




LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			H1	REVISED PER ECO-11-004917	11MAR11	RK HMR



- 1 . INSULATION DIA .082 MAX
- 2 . FITS TAB THK .020±.001



-	-	-
100	LOOSE PC,BOX	8-641321-1
-	TAPE MOUNTED	641321-2
-	LOOSE PIECE	641321-1
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
-

VOLTAGE RATING:
-

CIRCULAR MIL AREA:
-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
BODY,BRASS .016
SLV,NYLON,COLOR,YELLOW

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .015
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH
BODY,TIN

DWN
L OLMEDA
26JUN95

CHK
M ELLIS
26JUN95

APVD
B BARE
26JUN95

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

TE Connectivity

NAME
RECEPTACLE, 187 SERIES,
FASTON™, PIDG™,
26-24

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-641321

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
NTS

SHEET
1 OF 1

REV
H1

1470-19 (3/11)