





1. MATERIAL:
TERMINAL: PHOSPHOR BRONZE, THICKNESS=0.2mm.
2. FINISH:
TERMINAL: 2.0um MIN. TIN(MATTE) PLATE OVER 0.75um
MIN. NICKEL UNDERPLATE OVER ALL.
3. APPLY HOUSING PART NO: X-440146-X.
4. APPLICATION SPECIFICATION: 114-57016.
5. APPLICABLE WIRE RANGE: AWG #28-#32.

TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.15 2 PLC ±0.10 3 PLC ±0.05 ANGLES ±3'	DWN	O. HU 05-JUL-2004	 TE Connectivity		
	CHK	S. HOU 05-JUL-2004			
MATERIAL SEE NOTE	APVD	T. KE 05-JUL-2004	WIRE TO BOARD SOCKET, TERMINAL		
	PRODUCT SPEC 108-57225				
FINISH SEE NOTE	QUALIFICATION TEST REPORT 501-57229	LOC DW	SIZE A ₃	DRAWING NO C-1734193	REV P
	WEIGHT	SCALE --		SHEET 1 OF 2	

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT.



TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±0.15 2 PLC ±0.10 3 PLC ±0.05 ANGLES ±3'		DWN		O. HU		 TE Connectivity		
		05-JUL-2004		S. HOU				
MATERIAL SEE NOTE		CHK		05-JUL-2004		NAME WIRE TO BOARD SOCKET, TERMINAL		
		APVD		T. KE 05-JUL-2004				
FINISH SEE NOTE		PRODUCT SPEC						
		QUALIFICATION TEST REPORT						
		WEIGHT		LOC DW		SIZE A ₃	DRAWING NO C-1734193	REV P
				SCALE		SHEET		2 OF 2

LTR	REVISION RECORD	SEE SHEET 1.	ECO	DWN	CHK	DATE
-----	-----------------	--------------	-----	-----	-----	------