Pin Header Shrouded 2,54 mm

Series **093**



Rated current	3,0 A
Rated voltage	150 VRMS / VDC
Withstand voltage	500 VRMS for one minute
Material contact	Copper alloy
Material insulator	High temp. thermoplast UL94V-0
Operating temperature	-40°C to +105°C
Max. processing temper.	260°C for 10 seconds

All dimensions in mm.

pitch **2,54**

termination

contact size **□ 0,64**

max. pincount **064**

Product group **3**

Variation

1



2



3



no. of contacts	see figure left	see figure left	available in variation		
n	A	B			
006	15,28	5,08	1	2	3
008	17,82	7,62	1	2	3
010	20,36	10,16	1	2	3
012	22,90	12,70	1	2	3
014	25,44	15,24	1	2	3
016	27,98	17,78	1	2	3
020	33,06	22,86	1	2	3
024	38,14	27,94	1	2	3
026	40,68	30,48	1	2	3
030	45,76	35,56	1	2	3
034	50,84	40,64	1	2	3
040	58,46	48,26	1	2	3
050	71,16	60,96	1	2	3
060	83,86	73,66	1	2	3
064	88,94	78,74	1	2	3

PCB Layout







Plating:
T = Sn
F = Au
S = Selective Au

Packaging:
S = Standard
R = Reel

Cap:
0 = Without cap
1 = With cap

Order code: 093-?-???-0-?-B??

Variation (1,2,3) | No. of contacts | Plating contact (T,F,S) | Packaging (S,R) | Cap (0,1)

GARRY

www.mpe-connector.de

CS160212_V3

Mating series	101	430
see page	6-9	6-10

MPE-Garry GmbH • Schäfflerstraße 13 • 87629 Füssen • Germany • Phone: +49 (0) 83 62 / 91 56-0 • Fax: +49 (0) 83 62 / 91 56-500 • Email: vk@mpe-connector.de • www.mpe-connector.de